

TECHSPEC® 3mm Dia. x 9mm FL, NIR I Coated, Double-Convex Lens



Stock **#49-454**

3-4 DAYS

[Other Coating Options](#)

-

1

+

£53.13

ADD TO CART

Qty 1-9
£53.13
Qty 10+
£47.81
Volume Pricing
Request Quote

!

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
3.00 +0.0/-0.025

Back Focal Length BFL (mm):

8.46
Effective Focal Length EFL (mm): 9.00
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Substrate: ☐ N-BK7
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <3
Bevel: Protective bevel as needed
Center Thickness CT (mm): 1.60
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 1.35
Radius R₁=R₂ (mm): 9.02
Clear Aperture CA (mm): 2.5
f/#: 3.00
Focal Length Specification Wavelength (nm): 587.6
Numerical Aperture NA: 0.17
Type: Double-Convex Lens
Wavelength Range (nm): 600 - 1050
Damage Threshold, By Design: ☐ 7 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant