


[« See all 49 Products in Family](#)
[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Plano-Concave \(PCV\) Lenses](#) / [VIS-NIR Coated Plano-Concave \(PCV\) Lenses](#)
TECHSPEC®

3mm Diameter x -6 FL, VIS-NIR Coated, Plano-Concave Lens


 Stock #84-380 **7 In Stock** [Other Coating Options](#)

 - 1 + **£62^{.80}**
[ADD TO CART](#)

TECHSPEC VIS-NIR Coated Plano-Concave (PCV) Lenses



| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-9 | each £62.80 |
| Qty 10-25 | each £56.80 |
| Qty 26-49 | each £50.40 |
| Need More? | Request Quote |

Prices shown are exclusive of VAT/local taxes

| Product Downloads | |
|------------------------------|-----------------|
| STEP:stp | PDF Drawing:pdf |
| ISO 10110 Drawing | |
| IGES:igs | Zemax:zar |
| Zemax:zmx | eDrawing:eprt |
| Code V:seq | EO Spec Sheet |
| Download All | |

General

Type: Plano-Concave Lens

Physical & Mechanical Properties

| | |
|---|---|
| Diameter (mm): 3.00 +0.0/-0.025 | Bevel: Protective as needed |
| Center Thickness CT (mm): 1.00 | Center Thickness Tolerance (mm): ±0.05 |
| Centering (arcmin): <3 | Clear Aperture CA (mm): 2.7 |
| Edge Thickness ET (mm): 1.17 | |

Optical Properties

| | |
|---|---|
| Effective Focal Length EFL (mm): -6.00 | Substrate: ① N-SF11 |
| f/#: 2.00 | Numerical Aperture NA: 0.25 |
| Coating: VIS-NIR (400-1000nm) | Wavelength Range (nm): 400 - 1000 |
| Back Focal Length BFL (mm): -6.56 | Coating Specification: R _{abs} ≤ 0.25% @ 880nm R _{avg} ≤ 1.25% @ 400 - 870nm R _{avg} ≤ 1.25% @ 890 - 1000nm |

| | | | |
|--|-----------------------------------|------------------------------------|-------|
| Focal Length Specification Wavelength (nm): | 587.6 | Focal Length Tolerance (%): | ±1 |
| Radius R₁ (mm): | -4.71 | Surface Quality: | 20-10 |
| Damage Threshold, By Design: ⓘ | 5 J/cm ² @ 532nm, 10ns | Power (P-V) @ 632.8nm: | 1.5λ |
| Irregularity (P-V) @ 632.8nm: | λ/4 | | |

Regulatory Compliance

| | | | |
|-------------------|------------------|------------------------------------|-------------|
| RoHS 2015: | Compliant | Certificate of Conformance: | View |
| Reach 235: | Compliant | | |

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- AR Coated to Provide <1.25% Reflectance per Surface for 400 - 1000nm
- <0.25% Reflectance @ 880nm
- Designed for 0° Angle of Incidence
- Various Coating Options: **Uncoated**, **VIS-EXT**, **MgF₂**, **VIS 0°**, **YAG-BBAR**, **NIR I**, and **NIR II**

TECHSPEC® VIS-NIR Coated Plano-Concave (PCV) Lenses are designed to bend parallel input rays to diverge from one another on the output side of the lens causing this lens to have a negative focal length. These lenses can be used for balancing aberrations created by other lenses within a system due to their negative spherical aberration. Plano-Concave (PCV) lenses are commonly used in a variety of applications including image reduction, beam expansion and telescopes. TECHSPEC® VIS-NIR Coated Plano-Concave (PCV) Lenses are optimized for transmission (>99%) in the near-infrared. These lenses are also available **Uncoated**, **VIS-EXT**, **MgF₂**, **VIS 0°**, **YAG-BBAR**, **NIR I**, or with **NIR II** AR coating options.

Technical Information


Uncoated N-BK7 Typical Transmission



Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV - NIR spectra.

[Click Here to Download Data](#)

N-BK7 with MgF₂ Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with MgF₂ (400-700nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 1.75\% \text{ @ } 400 - 700\text{nm (N-BK7)}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

N-BK7 with VIS-EXT Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.5\% \text{ @ } 350 - 700\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

N-BK7 with VIS-NIR Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

- $R_{abs} \leq 0.25\% @ 880nm$
- $R_{avg} \leq 1.25\% @ 400 - 870nm$
- $R_{avg} \leq 1.25\% @ 890 - 1000nm$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

N-BK7 with VIS 0° Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with 0° (425-675nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

- $R_{avg} \leq 0.4\% @ 425 - 675nm$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

N-BK7 with YAG-BBAR Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with YAG-BBAR (500-1100nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

- $R_{abs} \leq 0.25\% @ 532nm$
- $R_{abs} \leq 0.25\% @ 1064nm$
- $R_{avg} \leq 1.0\% @ 500 - 1100nm$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

N-BK7 with NIR I Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with I (600 - 1050nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.5\% \text{ @ } 600 - 1050\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

N-BK7 with NIR II Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with II (750 - 1550nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{abs} \leq 1.5\% \text{ @ } 750 - 800\text{nm}$$

$$R_{abs} \leq 1.0\% \text{ @ } 800 - 1550\text{nm}$$


$$R_{avg} \leq 0.7\% \text{ @ } 750 - 1550\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

Coating Curves

VIS-NIR (400-1000nm)



SHIFT + SELECT an area on CURVE to zoom

Related Products



#12-869 - Small Lens Clamp for 1-3mm Dia. Optics
£128.00

Qty

Frequently Purchased Together



#43-627 - 2.5mm Dia., 0.5mm Thick, Uncoated, Sapphire Window
£23.00

Qty



#43-638 - 1.0mm Diameter, Sapphire Ball Lens
£22.60

Qty



#45-348 - 18mm Dia. x 30mm FL, MgF₂ Coated, Achromatic Doublet Lens
£84.00

Qty



#45-374 - 3.0mm Dia. x -6 FL, Uncoated, Plano-Concave Lens
£44.80

Qty

Resources

Media Type

- Application Note
- Glossary
- Technical Tool
- Video
- FAQ
- Trending in Optics

APPLICATION NOTE

Anti-Reflection (AR) Coatings

APPLICATION NOTE

An Introduction to Optical Coatings

APPLICATION NOTE

Understanding Optical Specifications

APPLICATION NOTE

Lens Geometry Performance Comparison

GLOSSARY

NIR (Near Infrared)

GLOSSARY

VIS/NIR Coating

[View More](#)
