

TECHSPEC<sup>®</sup> 12.5mm Dia. x 25.0mm FL, NIR II, Inked, Plano-Convex Lens



Stock **#38-401-INK** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

£45<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | £45.60 each                   |
| Qty 10-24      | £40.80 each                   |
| Qty 25-49      | £36.60 each                   |
| Need More?     | <a href="#">Request Quote</a> |

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Plano-Convex Lens

Type:

Physical & Mechanical Properties

|                      |                           |
|----------------------|---------------------------|
| 12.50 ±0.025         | Diameter (mm):            |
| <1                   | Centering (arcmin):       |
| 3.10 ±0.05           | Center Thickness CT (mm): |
| 1.49                 | Edge Thickness ET (mm):   |
| 11.5                 | Clear Aperture CA (mm):   |
| Protective as needed | Bevel:                    |

Optical Properties

|                                                                                                                        |                                                       |
|------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------|
| 25.00 @ 587.6nm                                                                                                        | Effective Focal Length EFL (mm):                      |
| 22.96                                                                                                                  | Back Focal Length BFL (mm):                           |
| NIR II (750-1550nm)                                                                                                    | Coating:                                              |
| R <sub>abs</sub> ≤1.5% @ 750 - 800nm<br>R <sub>abs</sub> ≤1.0% @ 800 - 1550nm<br>R <sub>avg</sub> ≤0.7% @ 750 - 1550nm | Coating Specification:                                |
| N-BK7                                                                                                                  | Substrate: <input type="checkbox"/>                   |
| 40-20                                                                                                                  | Surface Quality:                                      |
| 1.5λ                                                                                                                   | Power (P-V) @ 632.8nm:                                |
| λ/4                                                                                                                    | Irregularity (P-V) @ 632.8nm:                         |
| ±1                                                                                                                     | Focal Length Tolerance (%):                           |
| 12.92                                                                                                                  | Radius R <sub>1</sub> (mm):                           |
| 2.00                                                                                                                   | f/#:                                                  |
| 0.25                                                                                                                   | Numerical Aperture NA:                                |
| 750 - 1550                                                                                                             | Wavelength Range (nm):                                |
| 8 J/cm² @ 1064nm, 10ns                                                                                                 | Damage Threshold, By Design: <input type="checkbox"/> |

Regulatory Compliance

|      |                             |
|------|-----------------------------|
| View | Certificate of Conformance: |
|------|-----------------------------|

## Product Details

- AR Coated to Provide <0.7% Reflectance per Surface for 750 - 1550nm
- Designed for 0° Angle of Incidence
- Various PCX Coating Options: [Uncoated](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [VIS-EXT](#), and [YAG-BBAR](#)

TECHSPEC® NIR II Coated Plano-Convex Lenses have a positive focal length, making them ideal for collecting and focusing light in imaging applications. They are also useful in a variety of applications involving emitters, detectors, lasers, and fiber optics. TECHSPEC® NIR II Coated Plano-Convex Lenses are available in a wide variety of diameters and focal lengths. Identical designs of these PCX lenses are also offered [uncoated](#) or with broadband anti-reflective (BBAR) coatings, which include [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [VIS-EXT](#), and [YAG-BBAR](#).

## Technical Information





N-BK7

### Uncoated N-BK7 Typical Transmission



Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV - NIR spectra.

[Click Here to Download Data](#)

### N-BK7 with MgF<sub>2</sub> Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with MgF<sub>2</sub> (400-700nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 1.75\% \text{ @ } 400 - 700\text{nm (N-BK7)}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

### N-BK7 with VIS-EXT Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.5\% \text{ @ } 350 - 700\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

### N-BK7 with VIS-NIR Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{abs} \leq 0.25\% \text{ @ } 880\text{nm}$$

$$R_{avg} \leq 1.25\% \text{ @ } 400 - 870\text{nm}$$

$$R_{avg} \leq 1.25\% \text{ @ } 890 - 1000\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)



provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts

;