

[See all 1 Products in Family](#)

## 40 x 55mm FL, Grade 1, Double-Convex Lens



Stock #73-213 **CLEARANCE** 20+ In Stock

⊖ 1 ⊕ £7.<sup>96</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	£7.96 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

Double-Convex Lens **Type:**

#### Physical & Mechanical Properties

40.00 **Diameter (mm):**

#### Optical Properties

55.00 **Effective Focal Length EFL (mm):**

[View](#)

## Product Details

- Ideal for Experimenting and Prototyping Applications
- Quantities Extremely Limited, Buy While Supplies Last
- For Even More Deals, Check out [Mega Clearance: Optics](#)

Double-convex (DCX) lenses have two outward curved surfaces, a positive focal length and are useful for 1:1 imaging and in multi-element systems.

40 - 49.9mm Experimental Quality Double-Convex (DCX) Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.

**Note:** Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

## Technical Information

