See all 389 Products in Family

TECHSPEC® 40mm Dia., 1mm Thick, NIR I AR Coated Sapphire Window

Stock **#25-413** **5 In Stock**

- 1 + **£296**.00

ADD TO CART

Volume Pricing	
Qty 1-24	**£296.00** each
Qty 25-50	**£249.00** each
Qty 51-99	**£241.00** each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Protective Window

Physical & Mechanical Properties

Clear Aperture CA (mm):

36.00

Diameter (mm):

40.00 ±0.05

Thickness (mm):
1.00 ±0.05

Parallelism (arcmin):
≤3.5

Bevel:
Protective as needed

Clear Aperture (%):
≥90

Edges:
Fine Ground

Poisson's Ratio:
0.27

Young's Modulus (GPa):
435

Knoop Hardness (kg/mm^2):
1,900.00

Optical Properties

Coating:
NIR I (600-1050nm)

Substrate:
Sapphire (Al_2O_3)

Index of Refraction (n_d):
1.77

Surface Quality:
80-50

Abbe Number (v_d):
72.24

Birefringence (n_o-n_e):
0.008 for Visible Light Orthogonal to Optical Axis

Axis Orientation:
Random

Coating Specification:
R_{avg} ≤0.5% @ 600 - 1050nm

Wavelength Range (nm):
600 - 1050

Surface Flatness (P-V):
2λ (typical)

Material Properties

Density (g/cm^3):
3.97

Coefficient of Thermal Expansion CTE (10^{-6}/°C):
5.4 (Parallel to C-Axis)
4.3 (Perpendicular to C-Axis)

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View

Reach 235:
Compliant

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our custom manufacturing capabilities or submit an inquiry here.

Product Details

- Features Extreme Surface Hardness Chemical Resistance
- Transmits Wavelengths Ranging From UV to Mid-Infrared
- Thinner and Stronger than Standard Glass Windows
- Anti-Reflection Coating Options Covering 350 - 5000nm Available

TECHSPEC® Sapphire Windows are manufactured from single crystal sapphire, making them ideal for demanding applications (such as laser systems) because of their extreme surface hardness, high thermal conductivity, high dielectric constant and resistance to common chemical acids and alkalis. Sapphire is the second hardest crystal next to diamond and, because of their structural strength, sapphire windows can be made much thinner than other common windows with improved transmittance. Chemically, sapphire is single crystal aluminum oxide (Al2O3) and is useful in a transmission range from UV to mid-infrared or 330 - 5500nm when uncoated. TECHSPEC® Sapphire Windows are available with anti-reflection (AR) coatings to improve performance in the visible, NIR, and IR spectra with coating options covering 350 - 5000nm.

Technical Information









Compatible Mounts

;