

TECHSPEC®

3mm Dia. x 9mm FL VIS 0° Coated, UV Plano-Convex Lens



UV Fused Silica Plano-Convex (PCX) Lenses



Stock **#72-279** **8 In Stock**

-

1

+

£96<sup>.80</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | £96.80 each                   |
| Qty 6-25       | £77.60 each                   |
| Qty 26-49      | £72.80 each                   |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General






|                                                       |  |                                      |
|-------------------------------------------------------|--|--------------------------------------|
| Plano-Convex Lens                                     |  | Type:                                |
| Physical & Mechanical Properties                      |  |                                      |
| Diameter (mm):                                        |  | 3.00                                 |
| Centering (arcmin):                                   |  | <3                                   |
| Center Thickness CT (mm):                             |  | 1.30 ±0.05                           |
| Edge Thickness ET (mm):                               |  | 1.02                                 |
| Clear Aperture CA (mm):                               |  | 2.5                                  |
| Bevel:                                                |  | Protective as needed                 |
| Optical Properties                                    |  |                                      |
| Effective Focal Length EFL (mm):                      |  | 9.00 @587.6                          |
| Back Focal Length BFL (mm):                           |  | 8.11                                 |
| Coating:                                              |  | VS 0° (425-675nm)                    |
| Coating Specification:                                |  | R <sub>avg</sub> ≤0.4% @ 425 - 675nm |
| Substrate: <input type="checkbox"/>                   |  | Fused Silica (Corning 7980)          |
| Surface Quality:                                      |  | 20-10                                |
| Power (P-V) @ 632.8nm:                                |  | 3λ                                   |
| Irregularity (P-V) @ 632.8nm:                         |  | λ/2                                  |
| Focal Length Tolerance (%):                           |  | ±1                                   |
| Radius R <sub>1</sub> (mm):                           |  | 4.13                                 |
| f/#:                                                  |  | 3                                    |
| Numerical Aperture NA:                                |  | 0.17                                 |
| Wavelength Range (nm):                                |  | 425 - 675                            |
| Damage Threshold, Reference: <input type="checkbox"/> |  | 5 J/cm2 @ 532nm, 10ns                |
| Regulatory Compliance                                 |  |                                      |
| Certificate of Conformance:                           |  | <a href="#">View</a>                 |






## PRODUCT DETAILS


- AR Coated to Provide <0.4% Reflection per Surface for 425 - 675nm
  - Precision Fused Silica Substrate
  - Various Coating Options: [Uncoated](#), [MgF<sub>2</sub>](#), [UV-AR](#), [UV-VIS](#), [VIS-EXT](#), [VIS-NIR](#), [YAG-BBAR](#), [NIR I](#), and [NIR II](#)
- TECHSPEC® UV Fused Silica Plano-Convex (PCX) Lenses VS 0° Coated feature precision specifications and a [variety of coating options](#) on a broadband substrate. Fused Silica is commonly used in applications from the Ultraviolet (UV) through the Near-Infrared (NIR). Its low index of refraction, low coefficient of thermal expansion, and low inclusion content make it ideal for laser applications and harsh environmental conditions. TECHSPEC® UV Fused Silica Plano-Convex (PCX) Lenses VS 0° Coated feature industry leading diameter and centration specifications, making them ideal for integration into demanding imaging and targeting applications. These lenses are VS 0° coated to increase their coating performance in the visible region and are designed for 0 degrees angle of incidence.

## TECHNICAL INFORMATION



|                                                                                                                                                                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                                                                                            | <p>Typical transmission of a 3mm thick, uncoated fused silica window across the UV - NIR spectra.</p> <p><a href="#">Click Here to Download Data</a></p>                                                                                                                                                                                                                                                                                                                                                                              |
| <p><b>Fused Silica with MgF<sub>2</sub> Coating</b><br/><b>Typical Transmission</b></p>  | <p>Typical transmission of a 3mm thick fused silica window with MgF<sub>2</sub> (400-700nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{avg} \leq 1.75\% @ 400 - 700\text{nm}</math> (N-BK7)</p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>                                                                                                 |
| <p><b>Fused Silica with UV-AR Coating</b><br/><b>Typical Transmission</b></p>           | <p>Typical transmission of a 3mm thick fused silica window with UV-AR (250-425nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{abs} \leq 1.0\% @ 250 - 425\text{nm}</math><br/><math>R_{avg} \leq 0.75\% @ 250 - 425\text{nm}</math><br/><math>R_{avg} \leq 0.5\% @ 370 - 420\text{nm}</math></p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p> |
| <p><b>Fused Silica with UV-VIS Coating</b><br/><b>Typical Transmission</b></p>          | <p>Typical transmission of a 3mm thick fused silica window with UV-VIS (250-700nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{abs} \leq 1.0\% @ 350 - 450\text{nm}</math><br/><math>R_{avg} \leq 1.5\% @ 250 - 700\text{nm}</math></p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>                                                          |
| <p><b>Fused Silica with VIS-EXT Coating</b><br/><b>Typical Transmission</b></p>         | <p>Typical transmission of a 3mm thick fused silica window with VIS-EXT (350-700nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{abs} \leq 1.0\% @ 350 - 700\text{nm}</math></p>                                                                                                                                                                                                                                                 |

|                                                                                                                                                                                                      |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                                                                                                                     | <p><math>R_{avg} \leq 0.5\%</math> @ 350 - 700nm</p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>                                                                                                                                                                                                                                                                                                                              |
| <p data-bbox="577 430 1092 534"><b>Fused Silica with VIS-NIR Coating</b><br/><b>Typical Transmission</b></p>      | <p>Typical transmission of a 3mm thick fused silica window with VIS-NIR (400-1000nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{abs} \leq 0.25\%</math> @ 880nm<br/><math>R_{avg} \leq 1.25\%</math> @ 400 - 870nm<br/><math>R_{avg} \leq 1.25\%</math> @ 890 - 1000nm</p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p> |
| <p data-bbox="577 1098 1092 1202"><b>Fused Silica with VIS 0° Coating</b><br/><b>Typical Transmission</b></p>    | <p>Typical transmission of a 3mm thick fused silica window with VIS 0° (425-675nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{avg} \leq 0.4\%</math> @ 425 - 675nm</p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>                                                                                                     |
| <p data-bbox="577 1768 1092 1872"><b>Fused Silica with YAG-BBAR Coating</b><br/><b>Typical Transmission</b></p>  | <p>Typical transmission of a 3mm thick fused silica window with YAG-BBAR (500-1100nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{abs} \leq 0.25\%</math> @ 532nm<br/><math>R_{abs} \leq 0.25\%</math> @ 1064nm<br/><math>R_{avg} \leq 1.0\%</math> @ 500 - 1100nm</p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>      |
| <p data-bbox="577 2439 1092 2543"><b>Fused Silica with NIR I Coating</b><br/><b>Typical Transmission</b></p>     | <p>Typical transmission of a 3mm thick fused silica window with NIR I (600 - 1050nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{avg} \leq 0.5\%</math> @ 600 - 1050nm</p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>                                                                                                  |



## COATING CURVES

## CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).