

[See all 10 Products in Family](#)

TECHSPEC® 3mm Diameter 45° Rod Mirror Aluminum Coated



45° Rod Mirrors

Stock #54-094 **20+ In Stock**

1 £96.80

ADD TO CART

Volume Pricing

Qty 1-5	£96.80 each
Qty 6-25	£87.20 each
Qty 26-49	£77.60 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Rod Lens **Type:**

Coating on Elliptical Surface **Note:**

Physical & Mechanical Properties

Diameter (mm):

3.00 +0.00/-0.05

6.00

Length (mm):

Bevel:

Protective as needed

Length Tolerance (mm):

±0.1

Optical Properties

Coating:

Protected Aluminum (400-700nm)

Substrate:

N-BK7

Surface Quality:

40-20

Angle Tolerance (arcmin):

±10

Coating Specification:

R_{avg} >85% @ 400 - 700nm

Ray Deviation (°):

90

Wavelength Range (nm):

400 - 700

Coating Type:

Metal

Damage Threshold, By Design:

0.3 J/cm² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015:

Compliant

Reach 219:

Compliant

Certificate of Conformance:

[View](#)

Product Details

- Protected Aluminum Coating
- Reflect Light at 90°

TECHSPEC® 45° Rod Mirrors are designed for use in a variety of laser and imaging systems. The mirrors can be used to redirect laser light at 90°. Their small diameters make them ideal for use in fiberscope/borescope applications where size is critical. TECHSPEC 45° Rod Mirrors feature polished elliptical surfaces and ground circumferences and bases. These components are available in a range of micro sizes for integration into a host of OEM applications.

Technical Information

