

3mW 850nm Mini LDM Laser Diode Module



Stock #72-813 **1 In Stock**

⊖ 1 ⊕ £144.⁰⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1+ | £144.00 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads



General

Index Guided Diode, CW **Type:**

Mean Time To Failures MTTF @ 25° (hours):
≥88,000

Drive Circuitry:
Fully shielded, reverse polarity protected

Note:
Includes: Users Manual, Warning Label, and Focus Key

Type of Laser:

Diode

Laser Class - CDRH:

IIIb

Physical & Mechanical Properties

Weight (g):

9.5

Pointing Accuracy (mrad):

<25

Length of Leads (mm):

230

Length (mm):

37.00

Optical Properties

Wavelength (nm):

850.00

Wavelength Tolerance (nm):

±10nm

Wavelength Stability (nm/°C):

0.25

Beam Size at Nearest Focus (µm):

<25

Beam Diameter (mm):

4 x 2 at Aperture

Beam Divergence (mrad):

<0.5

Color:

IR

Focus Range (mm):

35mm - ∞

Electrical

Operating Current (mA):

<40

Output Power (mW):

3 (Maximum)

Output Power Tolerance (%):

±5

Hardware & Interface Connectivity

Power Supply:

Power Supply Required and Sold Separately.

USA: [#59-099](#)

Europe: Not Available

Japan: [#59-099](#)

Korea: Not Available

China: [#59-099](#)

Power Requirement:

3.5 - 5 VDC

Electrical Leads/ Pin Connections:

red (+), black (-)

Output Type:

Free Space

Environmental & Durability Factors

Operating Temperature (°C):

-10 to +55

Storage Temperature (°C):

-10 to +85

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 240:

[Compliant](#)

Product Details

- Line Generation Optics Available
- Bare Leads for Instrument Integration
- Focusable from 35mm to Infinity

Self-contained and miniature, laser diode modules offer a variety of features. They are an ideal replacement for a helium-neon laser in many applications, and offer the benefits of superior durability, small size, and a range of

wavelengths and powers. Elliptical output beams are produced using a user-adjustable glass focusing lens. Circular output beams are produced using a long focal length plastic lens and are suitable for long distance and alignment applications. Applications include use as pilot beams for alignment, bar code readers, measurement, dimensional scanning, robotic control, target designation, positioning, and analysis. Focusing tool included with all diode modules. Line Generator attachments are available for all diode modules listed. [Power Supply](#), required for operation, sold separately.

Note: Laser diode case is electrically isolated from supply voltage.

Technical Information

