

TECHSPEC® 40mm Dia. x 160mm FL, VIS 0°, Inked, Achromatic Lens



Stock **#47-740-INK** 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕

£151.30

ADD TO CART

Qty 1-5
£151.30
Qty 6+
£121.13
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
40.00 ±0.025

Effective Focal Length EFL (mm):

160.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 154.10
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 39.00
Centering (arcmin): <1
Center Thickness CT (mm): 12.50 ±0.20
Center Thickness CT 1 (mm): 8.50 ±0.10
Center Thickness CT 2 (mm): 4.00 ±0.10
Radius R ₁ (mm): 98.66
Radius R ₂ (mm): -70.73
Radius R ₃ (mm): -205.72
Edge Thickness ET (mm): 9.48
Substrate: N-BK7 / N-SF5
Surface Quality: 40-20
f/#: 4.00
Numerical Aperture NA: 0.13
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View