

# TECHSPEC® 40mm Dia. x 40mm FL, Uncoated, Double-Convex Lens



Stock #63-560 **17 In Stock** [Other Coating Options](#)

1 **£40<sup>.80</sup>**

**ADD TO CART**



Volume Pricing	
Qty 1-9	£40.80 each
Qty 10-24	£36.80 each
Qty 25-99	£32.60 each
Need More?	<a href="#">Request Quote</a>

Prices shown are exclusive of VAT/local taxes

### Product Downloads

- STEP:stp PDF Drawing:pdf
- ISO 10110 Drawing
- IGES:igs Zemax:zar
- Zemax:zmx eDrawing:eprt
- Code V:seq EO Spec Sheet
- [Download All](#)

## General

**Type:** Double-Convex Lens

## Physical & Mechanical Properties

<b>Diameter (mm):</b> 40.00 +0.0/-0.025	<b>Centering (arcmin):</b> <1
<b>Bevel:</b> Protective as needed	<b>Center Thickness CT (mm):</b> 8.50
<b>Center Thickness Tolerance (mm):</b> ±0.10	<b>Edge Thickness ET (mm):</b> 1.74
<b>Clear Aperture CA (mm):</b> 39.00	

## Optical Properties

<b>Back Focal Length BFL (mm):</b> 37.54	<b>Effective Focal Length EFL (mm):</b> 40.00
<b>Coating:</b> Uncoated	<b>Substrate:</b> <a href="#">N-SF11</a>
<b>Surface Quality:</b> 40-20	<b>Power (P-V) @ 632.8nm:</b> 1.5λ
<b>Irregularity (P-V) @ 632.8nm:</b> λ/4	<b>Radius R<sub>1</sub>=-R<sub>2</sub> (mm):</b> 60.85
<b>f/#:</b> 1.00	<b>Focal Length Specification Wavelength (nm):</b> 587.6

<b>Focal Length Tolerance (%)</b> : ±1	<b>Numerical Aperture NA</b> : 0.50
<b>Wavelength Range (nm)</b> : 400 - 2500	

## Regulatory Compliance

<b>RoHS 2015</b> : <b>Compliant</b>	<b>Certificate of Conformance</b> : <a href="#">View</a>
<b>Reach 235</b> : <b>Compliant</b>	

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).


## Product Details

- Ideal for Imaging Applications
- Minimize Aberrations Including Spherical and Coma
- **UV Fused Silica DCX Lenses** Available
- Anti-Reflection Coating Options: **MgF<sub>2</sub>**, **VIS 0°**, **VIS-NIR**, **NIR I**, **NIR II**, **VIS-EXT**, and **YAG-BBAR**

TECHSPEC® Uncoated Double-Convex (DCX) Lenses, also referred to as bi-convex lenses, have two positive, symmetrical faces with equal radii on both sides. These lenses are generally recommended for finite imaging applications with a conjugate ratio (ratio between object distance and image distance) between 0.2 and 5. At a conjugate ratio of 1, aberrations such as spherical aberration, chromatic aberration, coma, and distortion are minimized or canceled due to the symmetric lens design. TECHSPEC® Uncoated Double-Convex Lenses resist the effects from various aberrations in a lens design that are ultimately seen in performance and affect modulation transfer function (MTF), spot size, telecentricity, depth of field (DOF), and others. These lenses are available in a variety of substrates and coating options for the visible and NIR spectra.

## Technical Information


### Uncoated N-BK7 Typical Transmission



Typical transmission of a 3mm thick, uncoated BK7 window across the UV - NIR spectra.

[Click Here to Download Data](#)

### N-BK7 with MgF<sub>2</sub> Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with MgF<sub>2</sub> (400-700nm) coating @ 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 1.75\% \text{ @ } 400 - 700\text{nm (N-BK7)}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

### N-BK7 with VIS-EXT Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating @ 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.5\% \text{ @ } 350 - 700\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

### N-BK7 with VIS-NIR Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating @ 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{abs} \leq 0.25\% \text{ @ } 880\text{nm}$$


$$R_{avg} \leq 1.25\% \text{ @ } 400 - 870\text{nm}$$

$$R_{avg} \leq 1.25\% \text{ @ } 890 - 1000\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

### N-BK7 with VIS 0° Coating Typical Transmission



Typical transmission of a 3mm thick N-BK window with VIS 0° (425-675nm) coating @ 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.4\% @ 425 - 675\text{nm}$$

Data outside this range is not guaranteed and for reference only.

[Click Here to Download Data](#)

### N-BK7 with YAG-BBAR Coating Typical Transmission



Typical transmission of a 3mm thick N-BK window with YAG-BBAR (500-1100nm) coating @ 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{abs} \leq 0.25\% @ 532\text{nm}$$


$$R_{abs} \leq 0.25\% @ 1064\text{nm}$$

$$R_{avg} \leq 1.0\% @ 500 - 1100\text{nm}$$

Data outside this range is not guaranteed and for reference only.

[Click Here to Download Data](#)

### N-BK7 with NIR I Coating Typical Transmission



Typical transmission of a 3mm thick N-BK window with NIR I (600 - 1050nm) coating @ 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.5\% @ 600 - 1050\text{nm}$$

Data outside this range is not guaranteed and for reference only.

[Click Here to Download Data](#)

## N-BK7 with NIR II Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with NIR II (750 - 1550nm) coating 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{abs} \leq 1.5\%$  @ 750 - 800nm

$R_{abs} \leq 1.0\%$  @ 800 - 1550nm

$R_{avg} \leq 0.7\%$  @ 750 - 1550nm

Data outside this range is not guaranteed and for reference only.

[Click Here to Download Data](#)

## Related Products



UV Fused Silica Double-Convex (DCX) Lenses



Uncoated Plano-Convex (PCX) Lenses



Plano-Convex (PCX) and Simple Lens Kits



Optical Lens and Filter Mounts

## Frequently Purchased Together



#02-105 - 12.5mm Diameter Float Glass Window  
£12.00

Qty



#03-666 - 8.0 - 118.0 Optic Height, English Bar-Type Optic Holder  
£96.00

Qty



#03-676 - 7.0 - 40.0 Optic Height, English Bar-Type Optic Holder  
£84.80

Qty






#27-501 - 100mm Dia x 200mm Focal Length, PCX Condenser Lens  
£100.80

Qty



## Compatible Mounts

	Title	Type	Compare	Stock Number	Price	Buy
 	40.0mm Optic Dia., Optic Mount	Fixed		#64-566	£26.20 <a href="#">Request Quote</a>	10 In Stock <input type="text" value="1"/> 

# Resources

## Media Type

- Application Note
- Technical Tool
- Trending in Optics
- FAQ
- Glossary
- Video

APPLICATION NOTE

Anti-Reflection  
(AR) Coatings

APPLICATION NOTE

An  
Introduction to  
Optical  
Coatings

APPLICATION NOTE

Understanding  
Optical  
Specifications

APPLICATION NOTE

Lens Geometry  
Performance  
Comparison

TECHNICAL TOOL

SAG Calculator

TRENDING IN OPTICS

Future of  
Spherical  
Lenses

[View More](#)