

[See all 6 Products in Family](#)

40X Water Immersion Objective, Nikon CFI60 Apo NIR

See More by [Nikon](#)



Stock #75-368 **NEW** [CONTACT US](#)

⊖ 1 ⊕ £2,692⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	£2,692.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

MRD07420 **Model Number:**

Compatible Tube Lens Focal Length (mm):
Focal Length: 200mm

Microscope Objective **Type:**

Infinity Corrected **Style:**

Nikon **Manufacturer:**

Physical & Mechanical Properties

0.55 **Field of View (mm):**

58.50 **Length excluding Threads (mm):**

29 **Maximum Diameter (mm):**

120 **Weight (g):**

Optical Properties

N/A **Compatible Cover Glass Thickness (mm):**

0.025 **Horizontal Field of View, 1/2" Sensor:**

0.22 **Horizontal Field of View, 2/3" Sensor:**

40X **Magnification:**

0.80 **Numerical Aperture NA:**

3.5 **Working Distance (mm):**

22 **Field Number (mm):**

60.5 **Parfocal Length (mm):**

Water **Immersion Liquid:**

Sensor

2/3" **Maximum Sensor Format:**

Threading & Mounting

M25 x 0.75 **Mounting Threads:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Water Dipping Design for Live Imaging
- Optimized for Infrared (IR) and Multiphoton Microscopy
- High NA for Superior Resolution

Nikon CFI60 Water Dipping Objectives design allows direct immersion into aqueous samples, reducing optical aberrations and enabling high-resolution, live imaging of thick specimens. These objectives are designed with high numerical apertures and long working distances and are available in a variety of magnifications. Featuring M25 x 0.75 mounting threads, these objectives can be easily integrated into existing microscopy systems. Nikon CFI60 Water Dipping Objectives enable high-resolution, low-aberration imaging deep within living tissues by efficiently transmitting infrared light and correcting optical distortions specific to multiphoton and IR microscopy.

Technical Information

