

45° Fan Angle, 400 - 500nm AR Coated, High Precision Powell Lens



Stock **#70-133** **1 In Stock**

£260^{.00}

ADD TO CART

Volume Pricing

Qty 1-10	£260.00 each
Qty 11-49	£233.60 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Beam Shaping Lens Type:

Physical & Mechanical Properties

8.90 +0.00/-0.15 Dimensions (mm):

8.90 +0.00/-2.00 Height (mm):

1.3 Input Beam Diameter, $1/e^2$ (mm):

Optical Properties

N-SF6 Substrate:

BBAR (400-500nm) Coating:

400 - 500 Wavelength Range (nm):

$R_{\text{abs}} < 1.0\%$ @ 400 - 500nm Coating Specification:

1.458 Index of Refraction (n_d):

45.00 Fan Angle ($^\circ$):

Regulatory Compliance

[View](#) Certificate of Conformance:

Product Details

- Generate Uniform, Flat-Top Profile Over Entire Line
- Fan Angles from 1° to 75° Available
- AR Coated for 400 - 500nm or 500 - 850nm

Precision Powell Lenses, also known as aspheric line generators (ALGs), spread an input beam across a uniform line with a top-hat beam profile at a specified fan angle. These Powell lenses are produced through a precision manufacturing process to ensure high contained power, uniformity, and line straightness across the entire produced line, as well as superior part-to-part consistency. They are designed for a specific input beam diameter to provide best line uniformity; larger input beams will result in higher intensity at the ends of the generated line, while smaller will create a more Gaussian distribution. Precision Powell Lenses are ideal for use in machine vision and life science applications including 3D profile measurement, PCB inspection, line-scan SD-OCT, line-scan confocal microscopy, flow cytometry, and particle analysis.

;