

**TECHSPEC® 45° AOI, 25.0mm Square, Cold Mirror**



TECHSPEC High Performance Cold Mirrors

Stock **#64-448** **20+ In Stock**

⊖ 1 ⊕ £48.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-9	£48.00 each
Qty 10-25	£43.20 each
Qty 26-49	£41.20 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Cold Mirror **Type:**

**Physical & Mechanical Properties**

3.30 ±0.2 **Thickness (mm):**

**Dimensions (mm):**

25.0 x 25.0

**Dimensional Tolerance (mm):**  
+0.0/-0.2

**Length (mm):**  
25.00

**Width (mm):**  
25.00

### Optical Properties

**Transmission (%):**  
Dichroic Filter

**Coating Type:**  
Dielectric

**Coating:**  
Cold Mirror, 45°

**Surface Flatness (P-V):**  
4 - 6λ

**Wavelength Range (nm):**  
425 - 1150

**Substrate:**   
BOROFLOAT®

**Angle of Incidence (°):**  
45

**Coating Specification:**  
R<sub>avg</sub> ≥ 95% @ 400 - 690nm and T<sub>avg</sub> ≥ 90% @ 750 - 1200nm  
AR Coating: R<sub>avg</sub> < 1% @ 700 - 1150nm

**Surface Quality:**  
80-50

### Regulatory Compliance

**RoHS 2015:**  
Compliant

**Certificate of Conformance:**  
[View](#)



**Reach 247:**  
Compliant

## Product Details

- >95% Reflection from 400 - 690nm
- >90% Transmission from 750 - 1200nm
- Optimized for 0° or 45° Angle of Incidence

TECHSPEC® High Performance Cold Mirrors feature a multi-layer dielectric coating optimized for greater than 95% reflection of visible light and greater than 90% transmission of IR wavelengths. Cold mirrors are designed for use in any application where heat build-up can cause damage or adverse effects. For high power illumination, forced air cooling is recommended.

## Technical Information



Quote Your Size

## Compatible Mounts

---