

TECHSPEC[®] 4.5mm Dia. x 9.0mm FL, VIS-EXT Coated Plano-Convex Lens



Stock **#88-628** ☐ In Stock
[Other Coating Options](#)

-

1

+

£53.55

ADD TO CART

Qty 1-9
£53.55
Qty 10+
£48.24
Volume Pricing
Request Quote

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
4.50 +0.0/-0.025

Effective Focal Length EFL (mm):

9.00 @ 587.6nm
Back Focal Length BFL (mm): 7.41
Coating: VIS-EXT (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <3
Center Thickness CT (mm): 2.38 ±0.05
Edge Thickness ET (mm): 1.80
Radius R₁ (mm): 4.65
Clear Aperture CA (mm): 4.05
f/#: 2
Numerical Aperture NA: 0.25
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 700
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant