

46mm Diameter Unmounted, Linear Glass Polarizing Filter



Stock **#53-347** CLEARANCE CONTACT US

-

1

+

£28^{.85}

ADD TO CART

Volume Pricing	
Qty 1+	£28.85 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:
Linear Polarizer

Physical & Mechanical Properties

Diameter (mm):
46.00

2.40 ±0.2	Thickness (mm):
<3	Parallelism (arcmin):
+0.0/-0.2	Dimensional Tolerance (mm):
Protective as needed	Bevel:
Dichroic Polarizing Film on Glass	Construction:
Cut	Edges:

Optical Properties

100:1	Extinction Ratio:
Polymer Film on B270	Substrate: ☐
80-50	Surface Quality:
Single: ~30	Transmission (%):
400 - 700	Wavelength Range (nm):
4 - 6λ	Surface Flatness (P-V):
95	Polarization Efficiency (%):

Environmental & Durability Factors

-15 to +70	Operating Temperature (°C):
------------	-----------------------------


Regulatory Compliance


Compliant	RoHS 2015:
Compliant	Reach 209:
View	Certificate of Conformance:

PRODUCT DETAILS

- 95% Polarization Efficiency
 - 30% Typical Single Transmission of Unpolarized Light from 400 - 700nm
 - 0.15% Average Crossed Transmission from 400 - 700nm
 - Also Available [Mounted](#)
- Linear Glass Polarizing Filters feature 95% polarization efficiency with a typical single filter transmission of 30%. The filters have a 0.15% average crossed transmission from 400-700nm. These sandwich-design polarizing filters are constructed of dichroic polarizing film on glass. Linear Glass Polarizing Filters are ideal for OEM applications, prototyping, and laboratory projects. These lightweight plastic filters are also available [mounted](#).

TECHNICAL INFORMATION





CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).
