

[See all 96 Products in Family](#)

TECHSPEC® 40mm Dia. Protected Silver Coated, M10 ZERODUR® Mirror

See More by [SCHOTT Optical Components](#)



TECHSPEC ZERODUR M10 First Surface Mirrors

Stock #17-782 **1 In Stock**

⊖ 1 ⊕ £190⁴⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1-5 | £190.40 each |
| Qty 6-25 | £152.00 each |
| Qty 26-49 | £143.20 each |
| Need More? | Request Quote |

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Flat Mirror **Type:**

Physical & Mechanical Properties

40.00 +0.00/-0.20 **Diameter (mm):**

| | |
|----------------------|------------------------------|
| 5.00 ±0.20 | Thickness (mm): |
| Commercial Polish | Back Surface: |
| Protective as needed | Bevel: |
| 90 | Clear Aperture (%): |
| Ground | Edges: |
| 30 | Parallelism (arcsec): |

Optical Properties

| | |
|--|--|
| Metal | Coating Type: |
| Protected Silver (450-10000nm) | Coating: |
| λ/10 | Surface Flatness (P-V): |
| 450 - 10000 | Wavelength Range (nm): |
| ZERODUR® | Substrate: <input type="checkbox"/> |
| R _{avg} >98% @ 450 - 800nm R _{avg} >98.5% @ 2000 - 10,000nm | Coating Specification: |
| 20-10 | Surface Quality: |
| 0.5 J/cm ² @ 532nm & 1064nm, 10ns | Damage Threshold, Reference: <input type="checkbox"/> |

Material Properties

| | |
|-----|---|
| 0.1 | Coefficient of Thermal Expansion CTE (10⁻⁶/°C): |
|-----|---|

Regulatory Compliance

| | |
|-----------|------------------------------------|
| Compliant | RoHS 2015: |
| View | Certificate of Conformance: |
| Compliant | Reach 247: |

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Precision ZERODUR® Substrates
- λ/10 Flatness
- Low Coefficient of Thermal Expansion

TECHSPEC® ZERODUR® λ/10 First Surface Mirrors are well suited for applications where temperature fluctuation is a concern. The ZERODUR® substrates have a coefficient of thermal expansion (CTE) of ±0.10 x 10⁻⁶/°C, which is an order of magnitude lower than most glass types. The low CTE allows these mirrors to have a consistent reflected wavefront, even when exposed to environments with varying temperature or illumination sources with changing intensity. TECHSPEC® ZERODUR® λ/10 First Surface Mirrors feature precision polished substrates with λ/10 flatness and 20-10 surface quality. Multiple metallic and enhanced metallic coating options are available, allowing for these mirrors to be easily integrated into applications in both the visible and infrared spectrum.

Note: Surface flatness is measured before coating.

Coating Curves