

TECHSPEC®

483nm CWL, 25mm Dia, 31nm Bandwidth, Unmounted OD 6 Fluorescence Bandpass Filter



Stock **#18-389** 1 In Stock

[Additional Bandwidths](#)

-

1

+

£272⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	£272.00 each
Qty 6-25	£217.60 each
Qty 26-49	£204.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:

Bandpass Filter	
Compatible Fluorophore: FITC Excitation / CFP Emission	
Physical & Mechanical Properties	
Diameter (mm): 25.00 ±0.1	
Clear Aperture CA (mm): 22.50	
Thickness (mm): 2.00 ±0.1	
Construction: Unmounted	
Physical Durability: Adhesion per MIL-PRF-13830B, Section C.4.5.12 Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11 Cleaning per MIL-C-48497A Section 4.5.4.2	
Bevel: Protective as needed	
Optical Properties	
Angle of Incidence (°): 0 ±5	
Bandwidth (nm): 31.00	
OD 6 Blocking Wavelength Range (nm): 250 - 455 & 510 - 660	
Optical Density OD (Average): ≥6.0	
Average Transmission (%): >93 over Bandwidth	
Center Wavelength CWL (nm): 482.50	
Full Width-Half Max FWHM (nm): 36.00	
Substrate: Fused Silica (Corning 7980)	
Minimum Transmission (%): 93	
Coating: Hard Coated	
Surface Quality: 60-40	
Blocking Wavelength Range (nm): 250 - 1100	
Transmitted Wavefront, RMS: λ/4 (prior to coating)	
Environmental & Durability Factors	
Environmental Durability: Humidity per MIL-STD-810H, Section 507.6 Temperature per MIL-STD-810H, Section 501.7 and 502.7	
Regulatory Compliance	
RoHS 2015: Compliant	
Certificate of Conformance: View	
Reach 247: Compliant	

PRODUCT DETAILS

- Designed for Use With Common Fluorophores
 - Excitation and Emission Filters Available
 - High Transmission with Deep >OD 6.0 Blocking
 - Mounted [Fluorescence Filters](#) and [Mounted Fluorescence Filter Sets](#) Also Available
- TECHSPEC® Unmounted Fluorescence Bandpass Filters are designed with center wavelengths and bandwidths that match the excitation and emission wavelengths of common fluorophores. These filters feature high transmission up to >93% in their passband with deep >OD 6.0 blocking outside of their passband, resulting in high contrast images when used in fluorescence imaging systems. The low transmitted wavefront error of these filters further enhances image quality by minimizing image distortion. TECHSPEC Unmounted Fluorescence Bandpass Filters are available with a 12.5 or 25mm diameter and are ideal for integration into life science and biotech instrumentation including polymerase chain reaction (PCR) testing platforms, DNA sequencers, fluorescence detectors, flow cytometers, and fluorescence imaging systems.

CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).
