

TECHSPEC<sup>®</sup> 488nm, 12.5mm Diameter, OD 4.0 Notch Filter



TECHSPEC OD 4.0 Notch Filters

Stock **#67-108** **3 In Stock**

-

1

+

£256<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | £256.00 each                  |
| Qty 6-25       | £217.60 each                  |
| Qty 26-49      | £202.40 each                  |
| Need More?     | <a href="#">Request Quote</a> |

**i** Prices shown are exclusive of VAT/local taxes

Product Downloads

| General                          |                         |
|----------------------------------|-------------------------|
|                                  | Type:                   |
| Notch Filter                     |                         |
| Physical & Mechanical Properties |                         |
|                                  | Diameter (mm):          |
| 12.50 +0.00/-0.10                |                         |
|                                  | Clear Aperture CA (mm): |

|                                                                                                                                                     |                           |
|-----------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------|
| 10.6                                                                                                                                                |                           |
|                                                                                                                                                     | Thickness (mm):           |
| 5.00 ±0.1                                                                                                                                           |                           |
|                                                                                                                                                     | Construction:             |
| Mounted in Black Anodized Ring                                                                                                                      |                           |
|                                                                                                                                                     | Physical Durability:      |
| Adhesion per MIL-PRF-13830B, Section C.4.5.12<br>Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11<br>Cleaning per MIL-C-48497ASection 4.5.4.2 |                           |
|                                                                                                                                                     | Substrate Thickness (mm): |
| 3.5 ±0.5                                                                                                                                            |                           |

| Optical Properties |                                |
|--------------------|--------------------------------|
|                    | Optical Density OD (Average):  |
| ≥4.0               |                                |
|                    | Center Wavelength CWL (nm):    |
| 488.00             |                                |
|                    | Design Wavelength DWL (nm):    |
| 488                |                                |
|                    | Full Width-Half Max FWHM (nm): |
| 24.40              |                                |
|                    | Coating:                       |
| Hard Coated        |                                |
|                    | Surface Quality:               |
| 60-40              |                                |
|                    | Transmission (%):              |
| 90                 |                                |
|                    | Transmission Wavelength (nm):  |
| 365 - 650          |                                |
|                    | Reflection at CWL (%):         |
| 99                 |                                |
|                    | Transmitted Wavefront, RMS:    |
| <1λ                |                                |

| Threading & Mounting |                       |
|----------------------|-----------------------|
|                      | Mount Thickness (mm): |
| 5.0                  |                       |


| Environmental & Durability Factors                                                                |                           |
|---------------------------------------------------------------------------------------------------|---------------------------|
|                                                                                                   | Environmental Durability: |
| Humidity per MIL-STD-810H, Section 507.6<br>Temperature per MIL-STD-810H, Section 501.7 and 502.7 |                           |

| Regulatory Compliance |                             |
|-----------------------|-----------------------------|
|                       | RoHS 2015:                  |
| Compliant             |                             |
|                       | Certificate of Conformance: |
| View                  |                             |
|                       | Reach 247:                  |
| Compliant             |                             |


## Product Details

- >OD 4.0 Rejection of Laser Wavelength from 355nm to 1064nm
  - Broad Transmission Range
  - OD 6.0 Notch Filters Also Available
  - Low Cost Alternative to Rugate Notch Filters
- TECHSPEC® OD 4.0 Notch Filters are low-cost alternatives to Rugate Notch Filters. The filters feature narrow rejection bands of just ±2.5% of the center wavelength while offering greater than 99% reflection of the laser wavelength. These optical filters have a broad transmission range and are hard coated to guarantee performance that will not degrade with time, temperature, or humidity. TECHSPEC® OD 4.0 Notch Filters are mounted in a black anodized ring engraved to ease filter handling, identification, and orientation. OD 6.0 Notch Filters are also available for purchase.
- Note:** These filters are optimized for high spectral performance rather than high Laser Induced Damage Thresholds (LIDT). A typical LIDT for these filters is 1 J/cm<sup>2</sup> @ 532nm, 10ns. Please [contact us](#) if you require a filter with a higher LIDT value.

## Technical Information



This graph is an example of a standard notch filter transmission curve. For specific wavelength data, please refer to the curve PDF attached to each respective part.



All mounted TECHSPEC® Optical Filters have an arrow on the side of the mount that points to the filter-coated surface for quick reference. Filter oriented such that arrow points to filter coated surface S1. Anti-reflective (AR) coating is applied to S2.

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts