

TECHSPEC® 4mm Dia. x 6mm FL, MgF₂ Coated, Achromatic Doublet Lens



MgF₂ Coated Achromatic Lenses



Stock **#63-690** 3-4 DAYS

[Other Coating Options](#)

- 1 + **£81.60**

ADD TO CART

Qty 1-5
£81.60

Qty 6+
£65.24

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
4.00 +0.0/-0.025

Effective Focal Length EFL (mm): 6.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 3.92
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 3.6
Centering (arcmin): <3
Center Thickness CT (mm): 3.80 ±0.10
Center Thickness CT 1 (mm): 2.80 ±0.05
Center Thickness CT 2 (mm): 1.00 ±0.05
Radius R₁ (mm): 4.24
Radius R₂ (mm): -2.60
Radius R₃ (mm): -18.90
Edge Thickness ET (mm): 3.19
Substrate: ☐ N-BAF10 / N-SF10
Surface Quality: 20-10
f/#: 1.5
Numerical Aperture NA: 0.33
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View