

TECHSPEC® 4mm UC Series Fixed Focal Length Lens



4mm FL, #33-300



Stock **#33-300** ☒ In Stock

1

£221.00

ADD TO CART

Qty 1+

£221.00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Iris Option:
Variable

Length (mm):
40.60

Horizontal Field of View, 1/2" Sensor:
23.0mm - 84.8°

Filter Thread:

M62 x 0.75 with adapter #33-308
Maximum Diameter (mm): 40
Outer Diameter (mm): 40.00
Weight (g): 72
Horizontal Field of View, 1/3" Sensor: 15.6mm - 65.4°
Maximum Rear Protrusion (mm): 2.8
Maximum Image Circle (mm): 8.00
Numerical Aperture NA, Object Side: 0.0894
Horizontal Field of View @ Max Sensor Format: 23.0mm - 84.8°
Number of Elements (Groups): 8 (7)
Front Thread: M40 x 0.5 (Male)
Mounting Diameter (mm): 30.0
Horizontal Field of View, 1/2.5" Sensor: 20.0mm - 77.8°
Optimized Sensor Format: 1/2.5"
Type: Fixed Focal Length Lens
Focal Length FL (mm): 4.00
Primary Magnification PMA_G: 0.343
Maximum Sensor Format: 1/2"
Working Distance (mm): 0 - ∞
Mount: C-Mount
Aperture (f/#): f/1.8 - f/11
Coating: λ/4 MgF ₂
Coating Specification: λ/4 MgF ₂
Entrance Pupil Position (mm): 12.69
Horizontal Field of View, 1/4" Sensor: 11.2mm - 49.7°
Object Space Principal Plane (mm): 16.04
Image Space Principal Plane (mm): 5.84
Field of View at Max Sensor Format: Horizontal: 23.1mm - 84.8° Vertical: 15.7mm - 65.3° Diagonal: 33.7mm - 101.6°
Maximum Distortion (%): -20.43
Maximum Length (mm): 40.6
Exit Pupil Position (mm): -12.68
Lens Wavelength Range: VIS
Imaging Lens Type: High Performance Lens with Compact Form Factor
Storage Temperature (°C): -20 to +60 For questions regarding operating temperature please contact our support team

Regulatory Compliance

RoHS 2015: Compliant
--

REACH 201:
[Compliant](#)

Certificate of Conformance:
[View](#)