

42mm Radius, ±10° Tilt, Micro Manual Goniometer



Micro Manual Goniometers

Stock **#13-780** [CONTACT US](#)

-

1

+

£2,380⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£2,380.00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

English

Type:

Physical & Mechanical Properties

Goniometer

Type of Movement:

66 x 19.1

Stage Size (mm):

Travel (°):

±10	
17.50	Thickness (mm):
0.32	Leadscrew Pitch (mm):
0.45	Load Capacity, Normal (kg):
42	Radius R (mm):
2.6 x0.75	Stage Size (inches):
40	Weight (g):

Hardware & Interface Connectivity

Lead Screw	Type of Drive:
------------	----------------

Threading & Mounting

(10) 0-80	Mounting Threads:
-----------	-------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

Product Details

- Small Footprint
- Zero-Backlash Drive System
- 25mm or 42mm Radius Versions Stackable to Create 2-Axis Version

Micro Manual Goniometers offer fine angular adjustment within a very small 66mm x 19mm footprint, making them ideal for space-restricted requirements. These goniometers feature ±10° of angular travel with either a 25mm or a 42mm radius of rotation, and are ideal for fiber optic alignment or beam steering applications. Minimal backlash and a 0.32mm lead screw pitch ensure controlled and precise adjustments with the knurled adjustment knob. These Micro Manual Goniometers are compatible with [Micro Manual Positioning Stages](#) and [Micro Manual Rotary Stage](#) to easily create an extremely compact, highly adjustable movement system. Optical components can be mounted to the goniometer via ten #0-80 mounting holes.