

5.00" Adapter Plate Assembly



Stock **#53-925** 2 In Stock

-

1

+

£56^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	£56.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

Physical & Mechanical Properties

Construction:

Black Anodized Aluminum

Threading & Mounting

Mounting Threads:

(3) 1/4-20, (2) 1/4-20 S.H.C.S Slots

Regulatory Compliance

Certificate of Conformance:

Product Details

- Designed for Our Linear Positioning Stages and Slides
- Centered 1/4-20 Hole Enables Use with Posts and Post Holders

Our line of adapter plates are designed for our linear positioning stages and slides to permit a variety of breadboard applications. Convenient counterbored slots offer plenty of clearance room while allowing for adjustment of position. Although designed for direct mounting to a breadboard, each has a centered $\frac{1}{4}$ "-20 mounting hole for vertical positioning with our posts and post holders. The mounting holes "E" separated by dimension "F" match the slide/stage base counterbored mounting holes. Use dimension "A" to match the width for ball stages (not all slides conform to this).

Note: Stock number #53-922 has no slots, only 4 c'bored clearance holes for #1/4 SHCS.

For use with our **translation stages** and **ball bearing slides**.

This precision-machined adapter plate enables secure and flexible integration of linear positioning stages, slides, and breadboard-mounted systems. The centered 1/4-20 threaded hole supports vertical mounting using standard optical posts and post holders. Ideal for creating modular setups in lab environments, this adapter plate offers compatibility with a wide range of motion control components. The counterbored slots ensure adjustability while maintaining a stable, flush connection, making it a versatile solution for prototyping, alignment systems, or research instrumentation.

FAQ(s)

What components is this adapter plate compatible with?

It's designed to interface with Edmund Optics' linear translation stages, ball bearing slides, standard breadboards, and optical posts.

Can this adapter plate be used for vertical setups?

Yes, the centered 1/4-20 mounting hole allows secure vertical mounting with standard posts and post holders.

? What makes this adapter plate adjustable?

The counterbored slots provide adequate clearance, allowing for fine adjustment of the mounting position during setup or alignment.

❓ Does this plate support direct mounting to optical tables or breadboards?

Yes, it's fully compatible with common breadboard hole patterns for direct and stable mounting.

Technical Information

	A	B	C	D	E	F	Stock No.
1.25" Adapter Plate Assembly	1.25"	2.75"	2.00"	1.00"	4-40	0.88"	#53-922
1.75" Adapter Plate Assembly	1.75"	3.75"	3.00"	1.00"	6-32	1.12"	#53-923
2.62" Adapter Plate Assembly	2.62"	4.75"	4.00"	2.00"	1/4-20	2.00"	#53-924
5.00" Adapter Plate Assembly	5.00"	6.75"	6.00"	4.00"	1/4-20	4.00"	#53-925

Technical drawing of the adapter plate assembly. The front view shows a rectangular plate with dimensions A (width), B (height), C (internal width), and D (internal height). The top and bottom edges have rounded corners with a radius of 0.375. The top edge has two mounting holes with a diameter of 1/4-20 TPI (centered). The bottom edge has two mounting holes with a diameter of 1/4-20 TPI (centered). The side view shows the plate thickness with dimensions E (total thickness) and F (internal thickness). The side view also shows two mounting holes with a diameter of 1/4-20 TPI (centered). The side view also shows two slots for 1/4-20 S.H.C.S. (Standard Hardened Cold-Chamber Steel).