

TECHSPEC® 4.5mm Dia. x 9mm FL, VIS-NIR Coated, Double-Convex Lens



Stock **#47-894** 3-4 DAYS
[Other Coating Options](#)

- 1 + **£55.25**

ADD TO CART

Qty 1-9
£55.25
Qty 10+
£49.73
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
4.50 +0.0/-0.025

Back Focal Length BFL (mm):

8.16
Effective Focal Length EFL (mm): 9.00
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870 nm R _{avg} ≤1.25% @ 890 - 1000nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <3
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.38
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 1.80
Radius R ₁ =R ₂ (mm): 8.88
Clear Aperture CA (mm): 4.05
f/#: 2.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.25
Type: Double-Convex Lens
Wavelength Range (nm): 400 - 1000
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant