

[See all 4 Products in Family](#)

50.8mm Dia., 3mm Thick, Uncoated, ISP Optics Magnesium Fluoride (MgF₂) Window | MF-W-50-3

See More by [ISP Optics](#)



Stock **#24-486** CLEARANCE **4 In Stock**

-

1

+

£356⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£356.00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Protective Window	Type:
MF-W-50-3	Model Number:

Physical & Mechanical Properties

Bevel:

Protective as needed	
85	Clear Aperture (%):
43.18	Clear Aperture CA (mm):
50.80 +0.00/-0.13	Diameter (mm):
3.00 ±0.13	Thickness (mm):
Fine Ground	Edges:
415.00	Knoop Hardness (kg/mm²):
<3	Parallelism (arcmin):
0.27	Poisson's Ratio:
138	Young's Modulus (GPa):

Optical Properties

106.22	Abbe Number (v _d):
Uncoated	Coating:
1.377	Index of Refraction (n _d):
Magnesium Fluoride (MgF ₂)	Substrate:
2λ	Surface Flatness (P-V):
40-20	Surface Quality:
120 - 7000	Wavelength Range (nm):

Material Properties

13.7	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):
3.18	Density (g/cm³):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

Product Details

- Excellent Transmission from 0.12 to 7μm
- Rugged and Durable
- Resistant to Chemical Etching

ISP Optics Magnesium Fluoride (MgF₂) Windows feature a low refractive index and high transmission from the Deep UV (DUV) to the Mid-Wave Infrared (MMR), without the need for an Anti-Reflection (AR) coating. Magnesium Fluoride is extremely durable, being resistant to mechanical and thermal shock. Featuring strong resistance to chemical etching and stability in water, these windows are able to be used in harsh external environments. ISP Optics Magnesium Fluoride (MgF₂) Windows are ideal for a wide range of applications from use in the DUV for Hydrogen Lyman-alpha line applications and excimer laser applications, to applications requiring transparency across multiple wavelengths such as spectroscopy and fluoescence imaging.