

TECHSPEC[®] 488nm CWL, 12.5mm Dia., Hard Coated OD 4.0 10nm Bandpass Filter



TECHSPEC Hard Coated OD 4.0 10nm Bandpass Filters

Stock **#65-086** ☐ In Stock

☐ [Additional Bandwidths](#)

-

1

+

£140.25

ADD TO CART

Qty 1-5

£140.25

Qty 6+

£110.50

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.1

Angle of Incidence (°):
0

Optical Density OD (Average):

≥4.0
Clear Aperture CA (mm): 8.5
Center Wavelength CWL (nm): 488.00 ±2.0
Full Width-Half Max FWHM (nm): 10.00 ±2.0
Full Width-Half Max FWHM Tolerance (nm): ±2.0
Substrate:  Optical Glass
Minimum Transmission (%): ≥85
Coating: Hard Coated
Surface Quality: 80-50
Thickness Tolerance (mm): ±0.1
Type: Bandpass Filter
Typical Applications: Surf Green
Blocking Wavelength Range (nm): 200 - 1200
Construction: Mounted in Black Anodized Ring
Environmental Durability: Humidity per ML-STD-810H, Section 507.6 Temperature per ML-STD-810H, Section 501.7 and 502.7
Physical Durability: Adhesion per ML-PRF-13830B, Section C.4.5.12 Moderate abrasion per ML-PRF-13830B, Section C.4.5.11 Cleaning per ML-C-48497A Section 4.5.4.2
Mount Thickness (mm): 5.0 ±0.1
Substrate Thickness (mm): 3.5 ±0.5 typical

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View