

TECHSPEC® 50.8mm Dia. $\lambda/10$ Fused Silica Optical Flat



Stock #01-914-000 **20+ In Stock**

- 1 + £188⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-10 | £188.00 each |
| Qty 11-25 | £168.00 each |
| Qty 26-49 | £157.60 each |
| Need More? | Request Quote |

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Interferometry Window **Type:**

Physical & Mechanical Properties

Clear Aperture CA (mm):

| | |
|----------------------|--|
| 45.70 | |
| 2.00 +0.00/-0.04 | Diameter (inches): |
| 50.80 +0.00/-1.00 | Diameter (mm): |
| 0.50 ±0.06 | Thickness (inches): |
| 12.70 ±1.5 | Thickness (mm): |
| ≤3 | Parallelism (arcmin): |
| Protective as needed | Bevel: |
| Single Surface | Construction: |
| Fine Ground | Edges: |
| 0.16 | Poisson's Ratio: |
| 73 | Young's Modulus (GPa): |
| 522.00 | Knoop Hardness (kg/mm²): |

Optical Properties

| | |
|------------------------------|---|
| Uncoated | Coating: |
| Clear | Color: |
| Fused Silica | Substrate: <input type="checkbox"/> |
| 1.458 | Index of Refraction (n_d): |
| 60-40 | Surface Quality: |
| 67.8 | Abbe Number (v_d): |
| 200 - 2200 | Wavelength Range (nm): |
| λ10 | Surface Flatness (P-V): |

Material Properties

| | |
|---|---|
| 2.20 | Density (g/cm³): |
| 0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C) | Coefficient of Thermal Expansion CTE (10⁻⁶/°C): |

Regulatory Compliance

| | |
|---------------------------|------------------------------------|
| Compliant | RoHS 2015: |
| View | Certificate of Conformance: |
| Compliant | Reach 240: |

Product Details

- Sizes Ranging from ½" Diameter to 14" Diameter
- Each λ20 Flat 76.2mm and Larger Includes a Certificate of Calibration
- Available with Standard Metallic Mirror Coatings: [λ10 and λ20 Mirrors](#)

TECHSPEC® Single Surface Optical Flats are used as a reference (test plate) against which the flatness of an unknown surface may be compared. Each piece is precision polished by our master opticians and tested on a Zygo interferometer to insure the surface flatness. The secondary surfaces of our single surface flats are pitch polished to window quality for viewing the interference pattern. TECHSPEC Single Surface Optical Flats ship in a durable storage case for permanent protection. λ20 flats that are 76.2mm or larger also include a certificate of calibration.