

TECHSPEC[®] 50.8mm Dia. x 100mm FL, 8-12μm BBAR Coated, ZnSe Plano-Convex Lens

See More by [Coherent®](#)



TECHSPEC Zinc Selenide (ZnSe) Plano-Convex (PCX) Lenses

Stock #11-410 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕

£930.75

ADD TO CART

Qty 1-10

£930.75

Qty 11+

£837.67

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.80 +0.00/-0.10

Effective Focal Length EFL (mm):
100.00 @ 10.6μm

Back Focal Length BFL (mm): 98.09
Coating: BBAR (8000-12000nm)
Coating Specification: R _{avg} ≤0.5% @ 8 - 12μm
Substrate: ☐ Coherent® Infrared ZnSe
Surface Quality: 40-20
Power (P-V) @ 632.8nm: λ
Power (P-V) @ 10.6μm: λ10
Irregularity (P-V) @ 10.6μm: λ20
Centering, ETD (μm): ≤12.7
Center Thickness CT (mm): 4.60 ±0.10
Edge Thickness ET (mm): 2.28
Radius R₁ (mm): 140.27
Clear Aperture CA (mm): 45.72
f/#: 1.97
Numerical Aperture NA: 0.25
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 8000 - 12000
Bulk Absorption Coefficient (cm⁻¹): <0.0005 @ 10.6μm
Surface Roughness (Angstroms): <50 RMS

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View