

[See all 7 Products in Family](#)

TECHSPEC®

4X, 0.17 NA, UCf Objective



Stock

#26-686

8 In Stock

-

1

+

£193⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-2	£193.60 each
Qty 3-4	£180.80 each
Qty 5-9	£174.40 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Fluorite	Type:
Finite Conjugate	Style:
Manufacturer:	

Physical & Mechanical Properties

30.91	Length (mm):
29	Maximum Diameter (mm):
32	Weight (g):

Optical Properties

2.2	Horizontal Field of View, 2/3" Sensor:
3.52	Horizontal Field of View, 1.1" Sensor:
8.00	Focal Length FL (mm):
4X	Magnification:
0.17	Numerical Aperture NA:
3.92	Resolving Power (µm):
9.31	Depth of Field (µm):
9.3	Working Distance (mm):
400 - 700	Wavelength Range (nm):
17.6	Field Number (mm):

Sensor

1.1"	Maximum Sensor Format:
------	------------------------

Threading & Mounting

C-Mount	Mounting Threads:
---------	-------------------

Environmental & Durability Factors

+10 to +40	Operating Temperature (°C):
------------	-----------------------------

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

Product Details

- Compact Finite Conjugate Objectives
 - Mount Directly to a C-Mount Camera
 - Near Diffraction Limited performance
- TECHSPEC® UCf Objective Series are compact objectives that are finite conjugate by design, but achieve similar imaging performance of infinity corrected objectives and do not require a secondary tube lens to generate an image on the sensor. Available at 2X, 4X, 5X, 10X, 15X, and 20X magnifications. These objectives mount directly to a C-mount camera without additional extension tubes.