

[See all 13 Products in Family](#)

4X Objective, CFI Plan Achromatic

See More by [Nikon](#)



Stock #75-352 **NEW** [CONTACT US](#)

⊖ 1 ⊕ £181⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£181.60 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

MRL00042 **Model Number:**

Compatible Tube Lens Focal Length (mm):
Focal Length: 200mm

Microscope Objective **Type:**

Infinity Corrected **Style:**

Nikon

Manufacturer:

Physical & Mechanical Properties

5.5 Field of View (mm):

29.90 Length excluding Threads (mm):

27 Maximum Diameter (mm):

65 Weight (g):

Optical Properties

N/A Compatible Cover Glass Thickness (mm):

1.6 Horizontal Field of View, 1/2" Sensor:

2.2 Horizontal Field of View, 2/3" Sensor:

4X Magnification:

0.10 Numerical Aperture NA:

30 Working Distance (mm):

22 Field Number (mm):

59.9 Parfocal Length (mm):

N/A Immersion Liquid:

Sensor

2/3" Maximum Sensor Format:

Threading & Mounting

M25 x 0.75 Mounting Threads:

Regulatory Compliance

[View](#) Certificate of Conformance:

Product Details

- Exceptional Flat-Field Imaging
- High Numerical Apertures and Oil Immersion Options Available
- Wide Magnification Range (1X to 100X)

Nikon's CFI Plan Achromat Objectives deliver exceptional flat-field imaging ensuring sharp, distortion-free clarity across the entire field of view, making these objectives ideal for both visual inspection and high-precision digital imaging. With high numerical apertures and specialized oil immersion options available, these objectives offer enhanced resolution and light-gathering capability for demanding high-magnification applications. Nikon CFI Plan Achromat Objectives are available in 1X up to 100X magnification, providing solutions for low-magnification overviews or detailed high-resolution imaging. Color corrected for the entire visible spectrum; these objectives are suitable for brightfield and fluorescence observation in routine lab work and photomicrography.

Technical Information

