

[See all 389 Products in Family](#)

TECHSPEC® 50.8mm Dia., 3.18mm Thick, BBAR (2000-5000nm) AR Coated Sapphire Window



Stock **#16-013** **1 In Stock**

£442.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-24	£442.00 each
Qty 25-50	£338.00 each
Qty 51-99	£323.00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Protective Window **Type:**

Crystal **Type of Window:**

Physical & Mechanical Properties

45.72 **Clear Aperture CA (mm):**

50.80 ±0.05	Diameter (mm):
3.18 ±0.05	Thickness (mm):
≤3.5	Parallelism (arcmin):
Protective as needed	Bevel:
≥90	Clear Aperture (%):
Fine Ground	Edges:
0.27	Poisson's Ratio:
435	Young's Modulus (GPa):
1,900.00	Knoop Hardness (kg/mm²):

Optical Properties

BBAR (2000-5000nm)	Coating:
Sapphire (Al ₂ O ₃)	Substrate: <input type="checkbox"/>
1.77	Index of Refraction (n_d):
80-50	Surface Quality:
72.24	Abbe Number (v_d):
0.1 per Inch	Surface Roughness (µm):
0.008 for Visible Light Orthogonal to Optical Axis	Birefringence (n_o-n_e):
Random	Axis Orientation:
R _{avg} <1.5% @ 2000-5000nm R _{abs} <3.0% @ 2000-5000nm R _{avg} <1.75% @ 2000-4000nm	Coating Specification:
2000 - 5000	Wavelength Range (nm):
2λ (typical)	Surface Flatness (P-V):

Material Properties

3.97	Density (g/cm³):
5.4 (Parallel to C-Axis) 4.3 (Perpendicular to C-Axis)	Coefficient of Thermal Expansion CTE (10⁻⁶/°C):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Features Extreme Surface Hardness Chemical Resistance
- Transmits Wavelengths Ranging From UV to Mid-Infrared
- Thinner and Stronger than Standard Glass Windows
- Anti-Reflection Coating Options Covering 350 - 5000nm Available

TECHSPEC® Sapphire Windows are manufactured from single crystal sapphire, making them ideal for demanding applications (such as laser systems) because of their extreme surface hardness, high thermal conductivity, high dielectric constant and resistance to common chemical acids and alkalis. Sapphire is the second hardest crystal next to **diamond** and, because of their structural strength, sapphire windows can be made much thinner than other common windows with improved transmittance. Chemically, sapphire is single crystal aluminum oxide (Al_2O_3) and is useful in a transmission range from UV to mid-infrared or 330 - 5500nm when uncoated. TECHSPEC® Sapphire Windows are available with anti-reflection (AR) coatings to improve performance in the visible, NIR, and IR spectra with coating options covering 350 - 5000nm.

Technical Information

Sapphire Typical Transmission




Standard Visible & NIR AR Coatings on Sapphire



Infrared BBAR Coatings on Sapphire



**Infrared AR Coated Sapphire Windows
1mm Thickness**



Compatible Mounts