

[See all 13 Products in Family](#)

50 x 50mm, IR 850nm, MicroBrite High Intensity Edge-Lit Backlights

See More by [Advanced Illumination](#)



Advanced Illumination MicroBrite High Intensity Edge-Lit Backlights

Stock **#18-551** [CONTACT US](#)

- 1 + £700⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£700.00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

BT050050-850IC **Model Number:**

50,000 **LED Lifetime (hours):**

LED Illuminator **Type of Illumination:**

Note:
Optional Manual Intensity Adjustment [#86-887](#) and [#89-555](#) are Available

Advanced Illumination	Manufacturer:
Backlight	Geometry:

Constant	Illumination Mode:
----------	---------------------------

Physical & Mechanical Properties

70.3 x 54.71 x 11.33	Dimensions (mm):
54.43	Weight (g):

1.40 x 1.35	Active Area (inches):
-------------	------------------------------

Optical Properties

IR	Color:
850	Wavelength (nm):

Hardware & Interface Connectivity

Flying Leads	Connector:
24V	Input Voltage (V):

Environmental & Durability Factors

0 - 60	Operating Temperature (°C):
IP50	Environmental Rating:

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:

Contains SVHC(s)	Reach 233:
----------------------------------	-------------------

Product Details

- High Intensity Machine Vision Illuminator
 - Edge-to-Edge Uniform, Low Heat Illumination
 - Thin, Compact Form Factor
 - Optional Manual Intensity Adjustments ([#86-887](#) and [#89-555](#)) Recommended
- Advanced Illumination MicroBrite High Intensity Edge-Lit Backlights offer high performance machine vision backlighting in thin, compact housings and outperform higher cost comparable surface mount lights. These bright backlights produce low heat, uniform lighting. To simplify system integration, these thin backlights include a panel mount and are available in the most common machine vision wavelengths. Advanced Illumination MicroBrite High Intensity Edge-Lit Backlights feature ultra-thin profiles and are idea for applications including edge-detection, part location, hole detection and object gauging.

Note: Requires 24V power supply [#66-855](#). Manual Intensity Adjustment [#86-887](#) and [#89-555](#) are recommended and sold separately.