

TECHSPEC®

50 x 50mm Linear Polarizing Film (XP42-40)



Stock

#29-493

20+ In Stock

-

1

+

£21⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-10	£21.40 each
Qty 11-25	£18.80 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Linear Polarizer

Type:

Note:
Polarization axis is parallel to marking on protective film.

Physical & Mechanical Properties

50.0 x 50.0 +0.0/-0.5

Dimensions (mm):

0.40 ±0.05	Thickness (mm):
Polarizing Film	Construction:
Optical Properties	
Uncoated, Protective Film on Both Sides	Coating:
9000:1 (nominal at 555nm)	Extinction Ratio:
Polymer Film XP42-40	Substrate: ☐
Single: 42 ±2 Parallel: 36.4 Crossed: <0.004 (nominal at 555nm)	Transmission (%):
400 - 700	Wavelength Range (nm):
>99.98 (nominal at 555nm)	Polarization Efficiency (%):
42 ±2	Transmission, Single (%):
36.4	Transmission, Parallel (%):
<0.004 (nominal at 555nm)	Transmission, Crossed (%):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

- High Transmission of Unpolarized Light from 400 – 700nm
- Excellent Extinction Ratio of 9000:1
- Available in Custom Sizes
- [High-Temperature](#) Options Also Available


Ideal for a range of imaging applications, TECHSPEC® High Contrast Linear Polarizing Film (XP42) features an excellent extinction ratio and high transmission from 400 – 700nm. This polarizing film is offered in multiple thicknesses; thicker polarizing film has increased rigidity. Available in sheets, TECHSPEC® High Contrast Linear Polarizing Film (XP42) can be cut to fit any application need.

Note: Polarizer Film with adhesive available.

Immediate Custom Quotes Available

If you have a need for any round, square, or rectangular size of a TECHSPEC High Contrast Linear Polarizing Film (XP42) in dimensions between 3mm and 600mm, please visit our [Polarizing Film Tool](#). We'll provide an immediate quote, and can deliver the part to your requested size in approximately 3 weeks. A full list of standard manufacturing tolerances and restrictions are listed. For fully customized polymer polarizers to your requirements, visit our [Customized Polymer Polarizers Capabilities](#) page.

Technical Information





;