

[See all 10 Products in Family](#)

50mm Dia. UV Polarizing Film



Stock **#72-682** **5 In Stock**

⊖ 1 ⊕ £109⁰⁰

ADD TO CART

Volume Pricing

Qty 1-9	£109.60 each
Qty 10-25	£87.36 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Linear Polarizer

Type:

Note:

Outer 0.5mm edge is not functional due to loss of transparency during laser cutting. Delivered with protective film and paper overlayer on both sides marked to show polarization axis

Physical & Mechanical Properties

Diameter (mm):

50.00 ±0.2

0.19 (Nominal) **Thickness (mm):**

Polarizing Film **Construction:**

Optical Properties

Uncoated **Coating:**

1000:1 (avg @ 325nm-400nm)
6000:1 (avg @ 400nm-750nm) **Extinction Ratio:**

CTA (Cellulose Triacetate) **Substrate:**

320 - 750 **Wavelength Range (nm):**

39 (325nm-400nm) **Transmission, Single (%):**

0.04 (325nm-400nm) **Transmission, Crossed (%):**

Environmental & Durability Factors

Heat Resistance: 70°C dry
Cold Resistance: -20°C **Operating Temperature (°C):**

DIN ISO 9022-2-10-07
DIN ISO 9022-2-11-05
DIN ISO 9022-2-12-07
DIN ISO 9022-2-14-05 **Environmental Durability:**

15 - 25 **Storage Temperature (°C):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 253:**

Product Details

- High UV Transmission from 325 - 400nm
- 1000:1 Contrast From 325 - 400nm, 6000:1 Contrast From 400 - 750nm
- Thin, Versatile Polymer Substrate

Ultraviolet (UV) Linear Polarizing Film provides excellent contrast, and transmission up to 39% for P-Polarized Light in the UV and VIS ranges from 325-750nm. A range of rectangular sizes are available to accommodate small and large beam diameters as well as LED light sources. Ultraviolet (UV) Linear Polarizing Films are made with a durable, robust film substrate that is flexible and can be cut to size using scissors. This polarizing film is a cost-effective alternative to glass UV polarizers, and are ideal for use in industrial sensing, spectroscopy, and microscopy applications. [Near-Infrared \(NIR\) Linear Polarizing Film](#) and Visible [TECHSPEC High Contrast Linear Polarizing Film \(XP42\)](#) are also available.