

TECHSPEC[®] 50.8mm Dia. x 200mm FL, 266nm Coated, Laser Grade PCX Lens



TECHSPEC Laser Grade PCXLenses

Stock **#70-015 3 In Stock**
☐ [Other Coating Options](#)

-

1

+

£348⁸⁰

ADD TO CART

Volume Pricing	
Qty 1+	£348.80 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Plano-Convex Lens	Type:
Physical & Mechanical Properties	
50.80 +0.00/-0.025	Diameter (mm):
<1	Centering (arcmin):

8.00	Center Thickness CT (mm):
4.41	Edge Thickness ET (mm):
45.72	Clear Aperture CA (mm):
Protective as needed	Bevel:

Optical Properties

200.00 @ 355nm	Effective Focal Length EFL (mm):
194.515	Back Focal Length BFL (mm):
Laser V-Coat (266nm)	Coating:
R _{abs} <0.25% @ 266nm	Coating Specification:
Fused Silica (Corning 7980)	Substrate: ☐
10-5	Surface Quality:
λ	Power (P-V) @ 632.8nm:
N/10 ±1	Irregularity (P-V) @ 632.8nm:
91.69	Radius R ₁ (mm):
3.94	f/#:
0.13	Numerical Aperture NA:
266	Design Wavelength DWL (nm):
3 J/cm² @ 266nm, 20ns, 20Hz	Damage Threshold, By Design: ☐

Regulatory Compliance

View	Certificate of Conformance:
------	-----------------------------

Product Details

- Guaranteed Laser Damage Threshold
- 10-5 Surface Quality
- N/10 Surface Accuracy

TECHSPEC® Laser Grade PCXLenses are designed for high energy Nd:YAG laser applications including laser cutting, machining, and welding. The precision fused silica substrate, featuring N/10 surface accuracy and 10-5 surface quality, ensures low scatter and excellent transmitted wavefront performance. TECHSPEC® Laser Grade PCXLenses are available uncoated or with a variety of high laser damage threshold anti-reflection (AR) coating options. Coatings are available at the most common Nd:YAG laser wavelengths to ensure maximum laser throughput.


LASER OPTICS

MADE BY EDMUND OPTICS®



LEARN MORE

Technical Information





Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
 - High-precision surface quality and flatness
 - Tight tolerances and complex geometries
 - Scalable production—from prototype to volume
- Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).