

50mm Diameter, 45° AOI, Hot Mirror



Hot Mirrors

Stock **#55-233** 15 In Stock

-

1

+

£55¹⁶

ADD TO CART

Volume Pricing	
Qty 1-9	£55.16 each
Qty 10-25	£49.46 each
Qty 26-49	£46.84 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Dichroic Filter

Type:

Physical & Mechanical Properties	
50.00 ±0.25	Diameter (mm):
3.30	Thickness (mm):
Optical Properties	
45.00	Angle of Incidence (°):
Hot Mirror, 45°	Coating:
BOROFLOAT®	Substrate: □
>90, 750 - 1125nm	Reflection (%):
80-50	Surface Quality:
>85, 425 - 675nm	Transmission (%):
Surface 1: 45° Hot Mirror Surface 2: None	Coating Specification:
425 - 1125	Wavelength Range (nm):
4 - 6λ	Surface Flatness (P-V):
Dielectric	Coating Type:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

PRODUCT DETAILS

- Ideal for Reducing Heat
- Reflects >90% of the NIR and IR
- Transmits >85% of Visible Light

Hot Mirrors are available in 0° or 45° angle of incidence options and are ideal for decreasing the undesirable heat caused by infrared radiation. A multi-layer dielectric coating transmits 85% of visible light while reflecting over 90% of the NIR and IR, making them suited for projection systems where heat build-up can lead to system damage.

Note: When using high power illumination, forced air cooling is recommended.

Hot mirrors are crucial in many projection and illumination systems where high levels of heat can quickly damage sensitive components. Hot mirrors are specially coated to transmit visible light while reflecting the NIR, a major attributor to heat generation. By using a hot mirror, heat levels are limited with minimum impact on the overall system performance.

QUOTE YOUR SIZE

COMPATIBLE MOUNTS