

[See all 40 Products in Family](#)

TECHSPEC® 515nm, 76.2mm Dia. x 12.7mm Thickness, Ultrafast Laser Mirror



Stock #73-715 **NEW** 3 In Stock

- 1 + £593.⁶⁰

ADD TO CART

Volume Pricing	
Qty 1+	£593.60 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Laser Mirror **Type:**

Physical & Mechanical Properties

6.35 ±0.20 **Thickness (mm):**

76.20 +0.00/-0.10 **Diameter (mm):**

90 **Clear Aperture (%):**

Commercial Polish **Back Surface:**

Parallelism (arcmin):
<3

Optical Properties

Fused Silica **Substrate:**

Surface Quality:
10-5

Angle of Incidence (°):
45

Coating:
Ultrafast (500-530nm)

Design Wavelength DWL (nm):
515

Wavelength Range (nm):
480 - 530

Surface Flatness (P-V):
 $\lambda/8$

Coating Specification:
 $R_{(avg)} S \& P > 99.90\% @ 515nm @ 45^\circ AOI$
 $R_{(avg)} > 99.7\% @ 500 - 530nm @ 45^\circ AOI$

Coating Type:
Dielectric

GDD Specification:
 $\pm 10 fs^2 @ 480 - 540nm @ 45^\circ AOI$ (s-pol) $\pm 20 fs^2 @ 500 - 530nm @ 45^\circ AOI$ (p-pol)

Damage Threshold, Pulsed:
0.2 J/cm², 150fs @ 515nm

Environmental & Durability Factors

Durability:
ML-PRF-13830B

Regulatory Compliance

Certificate of Conformance:
[View](#)

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- GDD as Low as $\pm 20 fs^2$ at Design Wavelength Range
- Greater than 99.9% Reflectivity
- Ideal for Ti:sapphire and Yb:doped Ultrafast Lasers

TECHSPEC® Low GDD Dielectric Ultrafast Laser Mirrors feature a multilayer dielectric coating on fused silica substrates for excellent reflectivity of greater than 99.9%, and low coefficient of thermal expansion, making them ideal for ultrafast beam transport applications. These mirrors have a group delay dispersion (GDD) of near zero at their design wavelength range, minimizing dispersion of the reflected beam. TECHSPEC® Low GDD Dielectric Ultrafast Laser Mirrors are ideal for utilizing the first and second harmonic of Ti:sapphire and Yb:doped lasers for applications such as laser machining and welding.

Note: Please [contact us](#) if your application requires a TECHSPEC Low GDD Ultrafast Mirror with a custom wavelength, angle, or size.