

[See all 64 Products in Family](#)

# Coherent® StingRay™ Laser Diode Module 1253668 | 520nm, 10mW

See More by [Coherent®](#)



Stock **#87-522** [CONTACT US](#)

-

 1 

+

**£771<sup>.00</sup>**

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | <b>£771.00</b> each           |
| Need More?     | <a href="#">Request Quote</a> |

**i** Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

## Product Downloads



### General

|           |                            |
|-----------|----------------------------|
| Coherent® | <b>Manufacturer:</b>       |
| Diode     | <b>Type of Laser:</b>      |
|           | <b>Laser Class - CDRH:</b> |

|                                                                                                                                                                                                                                      |                                    |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------|
| IIIb                                                                                                                                                                                                                                 |                                    |
| 1253668                                                                                                                                                                                                                              | Model Number:                      |
| Physical & Mechanical Properties                                                                                                                                                                                                     |                                    |
| <10                                                                                                                                                                                                                                  | Pointing Stability (μrad/°C):      |
| 95.10                                                                                                                                                                                                                                | Length (mm):                       |
| Optical Properties                                                                                                                                                                                                                   |                                    |
| TEM <sub>00</sub>                                                                                                                                                                                                                    | Spatial Mode:                      |
| 520.00                                                                                                                                                                                                                               | Wavelength (nm):                   |
| <1.5                                                                                                                                                                                                                                 | Mode Quality, M <sup>2</sup> :     |
| ±10                                                                                                                                                                                                                                  | Wavelength Tolerance (nm):         |
| Green                                                                                                                                                                                                                                | Color:                             |
| Electrical                                                                                                                                                                                                                           |                                    |
| 10                                                                                                                                                                                                                                   | Output Power (mW):                 |
| Max Analog: 500                                                                                                                                                                                                                      | Modulation Frequency (kHz):        |
| Hardware & Interface Connectivity                                                                                                                                                                                                    |                                    |
| Power Supply:<br>Power Supply Required and Sold Separately.<br>USA: <a href="#">#86-878</a><br>Europe: <a href="#">#86-878</a><br>Japan: <a href="#">#86-878</a><br>Korea: <a href="#">#86-878</a><br>China: <a href="#">#86-878</a> |                                    |
| Hirose HR-10P-12S                                                                                                                                                                                                                    | Electrical Leads/ Pin Connections: |
| Free Space                                                                                                                                                                                                                           | Output Type:                       |
| 5 - 24 DC                                                                                                                                                                                                                            | Input Voltage (V):                 |
| Environmental & Durability Factors                                                                                                                                                                                                   |                                    |
| 10 to 40                                                                                                                                                                                                                             | Operating Temperature (°C):        |
| -20 to +60                                                                                                                                                                                                                           | Storage Temperature (°C):          |
| Regulatory Compliance                                                                                                                                                                                                                |                                    |
| <a href="#">Exempt</a>                                                                                                                                                                                                               | RoHS 2015:                         |
| <a href="#">Contains SVHC(s)</a>                                                                                                                                                                                                     | Reach 224:                         |
| <a href="#">View</a>                                                                                                                                                                                                                 | Certificate of Conformance:        |

## Product Details

For CDRH certified systems, class IIIb lasers require [#86-878](#). These lasers include a Hirose connector and flying lead terminals for compatibility with a variety of power supplies.

- External Focus with up to 100mW Output Power
- Auto Scaling Input Power 5 - 24VDC with Reverse Polarity Protection
- Built-In Microcontroller for Fault Monitor
- [Coherent® StingRay™ Developer's Kit](#) also available

Coherent® StingRay™ and BioRay™ Laser Diode Modules are ideal for a variety of alignment, machine vision, and biomedical applications. They are available in a wide range of output powers, wavelengths, and fan angles. High precision optical components and sophisticated drive electronics provide power and control to your application, reducing signal-to-noise ratios and increasing measurement speed. Coherent® StingRay™ and BioRay™ Laser Diode Modules are designed with a flat top power distribution across the beam profile for consistency in line projection widths.

**Note:** For CDRH certified systems (Class IIIb), [#86-878](#) Laser Controller and additional external voltage source (0.5–5V) with BNC connector is required.

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries

- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

---

;