

[See all 245 Products in Family](#)

TECHSPEC[®] 50mm Dia. x 200mm FL, Uncoated, UV Double-Convex Lens



UV Fused Silica Double-Convex (DCX) Lenses



Stock **#22-429** **3 In Stock**

☐ [Other Coating Options](#)

-

1

+

£252⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	£252.00 each
Qty 6-25	£201.60 each
Qty 26-49	£188.80 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Double-Convex Lens

Physical & Mechanical Properties

50.00 +0.0/-0.025	Diameter (mm):
<1	Centering (arcmin):
Protective as needed	Bevel:
4.67 ±0.10	Center Thickness CT (mm):
1.23	Edge Thickness ET (mm):
49.00	Clear Aperture CA (mm):

Optical Properties	
198.39	Back Focal Length BFL (mm):
200.00	Effective Focal Length EFL (mm):
Uncoated	Coating:
Uncoated	Coating Specification:
Fused Silica (Corning 7980)	Substrate: ☐
40-20	Surface Quality:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
182.65	Radius R ₁ =R ₂ (mm):
4.00	f/#:
587.6	Focal Length Specification Wavelength (nm):
±1	Focal Length Tolerance (%):
0.13	Numerical Aperture NA:
200 - 2200	Wavelength Range (nm):

Regulatory Compliance	
View	Certificate of Conformance:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details




- Ideal for Imaging Applications
- Minimize Aberrations Including Spherical and Coma
- Precision Fused Silica Substrate

TECHSPEC® UV Fused Silica Double-Convex (DCX) Lenses, also referred to as bi-convex lenses, have two positive, symmetrical faces with equal radii on both sides. These lenses are generally recommended for finite imaging applications with a conjugate ratio (ratio between object distance and image distance) between 0.2 and 5. At a conjugate ratio of 1, aberrations such as spherical aberration, chromatic aberration, coma, and distortion are minimized or canceled due to the symmetric lens design. TECHSPEC® UV Fused Silica Double-Convex (DCX) Lenses have a precision fused silica substrate. These lenses are available uncoated or with UV-AR, UV-VIS, VIS-EXT, VIS-NIR, VIS 0°, NIR I, or NIR II coatings.






Technical Information







UV FS Transmission Curve



FUSED SILICA																									
Uncoated Fused Silica Typical Transmission <table border="1"><caption>Approximate data for Uncoated Fused Silica Transmission</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>92</td></tr><tr><td>400</td><td>94</td></tr><tr><td>600</td><td>94</td></tr><tr><td>800</td><td>94</td></tr><tr><td>1000</td><td>94</td></tr><tr><td>1200</td><td>94</td></tr><tr><td>1400</td><td>92</td></tr><tr><td>1600</td><td>94</td></tr><tr><td>1800</td><td>94</td></tr><tr><td>2000</td><td>94</td></tr><tr><td>2200</td><td>90</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	92	400	94	600	94	800	94	1000	94	1200	94	1400	92	1600	94	1800	94	2000	94	2200	90	Typical transmission of a 3mm thick, uncoated fused silica window across the UV - NIR spectra. Click Here to Download Data
Wavelength (nm)	Transmission T (%)																								
200	92																								
400	94																								
600	94																								
800	94																								
1000	94																								
1200	94																								
1400	92																								
1600	94																								
1800	94																								
2000	94																								
2200	90																								
Fused Silica with MgF₂ Coating Typical Transmission <table border="1"><caption>Approximate data for Fused Silica with MgF₂ Coating Transmission</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>94</td></tr><tr><td>400</td><td>97</td></tr><tr><td>600</td><td>97</td></tr><tr><td>800</td><td>96</td></tr><tr><td>1000</td><td>96</td></tr><tr><td>1200</td><td>96</td></tr><tr><td>1400</td><td>93</td></tr><tr><td>1600</td><td>96</td></tr><tr><td>1800</td><td>96</td></tr><tr><td>2000</td><td>96</td></tr><tr><td>2200</td><td>90</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	94	400	97	600	97	800	96	1000	96	1200	96	1400	93	1600	96	1800	96	2000	96	2200	90	Typical transmission of a 3mm thick fused silica window with MgF₂ (400-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 1.75\% \text{ @ } 400 - 700\text{nm (N-BK7)}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Wavelength (nm)	Transmission T (%)																								
200	94																								
400	97																								
600	97																								
800	96																								
1000	96																								
1200	96																								
1400	93																								
1600	96																								
1800	96																								
2000	96																								
2200	90																								
Fused Silica with UV-AR Coating Typical Transmission																									

	Typical transmission of a 3mm thick fused silica window with UV-AR (250-425nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.0\% @ 250 - 425\text{nm}$ $R_{avg} \leq 0.75\% @ 250 - 425\text{nm}$ $R_{avg} \leq 0.5\% @ 370 - 420\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with UV-VIS Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with UV-VIS (250-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.0\% @ 350 - 450\text{nm}$ $R_{avg} \leq 1.5\% @ 250 - 700\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with VIS-EXT Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with VIS-EXT (350-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\% @ 350 - 700\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with VIS-NIR Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with VIS-NIR (400-1000nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\% @ 880\text{nm}$ $R_{avg} \leq 1.25\% @ 400 - 870\text{nm}$ $R_{avg} \leq 1.25\% @ 890 - 1000\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with VIS 0° Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with VIS 0° (425-675nm) coating at 0° AOI.

	The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.4\% @ 425 - 675\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with YAG-BBAR Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with YAG-BBAR (500-1100nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\% @ 532\text{nm}$ $R_{abs} \leq 0.25\% @ 1064\text{nm}$ $R_{avg} \leq 1.0\% @ 500 - 1100\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with NIR I Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with NIR I (600 - 1050nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\% @ 600 - 1050\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with NIR II Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with NIR II (750 - 1550nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.5\% @ 750 - 800\text{nm}$ $R_{abs} \leq 1.0\% @ 800 - 1550\text{nm}$ $R_{avg} \leq 0.7\% @ 750 - 1550\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data