

532nm 0 - 250mW, Fiber-Coupled Laser



Fiber-Coupled Laser System

Stock **#33-048** CLEARANCE 3-4 DAYS

-

1

+

£5,368.56

ADD TO CART

Qty 1+

£5,368.56

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Operating Temperature (°C):
+10 to +30

Output Power (mW):
250 (Maximum)

Dimensions (mm):
76.2 L x 152.4 W x 254.0 H

Fiber Diameter (µm):
400.00

Wavelength (nm):

532.00
Weight (kg): 1.13
Wavelength Tolerance (nm): ±5
Operating Humidity: 5 to 95%, non-condensing
Length of Cable (m): 0.5
Cooling Method: TE Cooled with forced air
Beam Divergence (NA): 0.22, Nominal
Output Type: Fiber-Coupled
Type of Laser: Diode
Laser Class - CDRH: IIIb
Color: Green
Connector: SMA
Input Voltage (V): 100 - 240 AC
Bandwidth (nm): <3

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View