

532nm, 25.4mm Dia., Diffractive Vortex Phase Plate



HOLO/OR Diffractive Vortex Phase Plates

Stock #14-744 3-4 DAYS

- 1 + **£3,845.40**

ADD TO CART

Qty 1+
£3,845.40

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Clear Aperture CA (mm):
22.9

Coating:
Laser V-Coat (532nm)

Design Wavelength DWL (nm):
532

Diameter (mm):
25.40 +0.05/-0.15

Substrate: Fused Silica (Corning 7980)
Thickness (mm): 3.00 ±0.1
Input Beam Mode: SMTEM ₀₀
Overall Efficiency (%): 95
Topological Charge: 1
Outer Ring Size (Diffraction Limits): 2.02
Damage Threshold, Reference: ☐ See Link for More Details

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant