

TECHSPEC® 50mm Dia. x 250mm FL, VIS 0° Inked, Double-Convex Lens



Stock **#48-264-INK** [CONTACT US](#)

[Other Coating Options](#)

- 1 + **£63.75**

ADD TO CART

Qty 1-9
£63.75
Qty 10+
£57.38
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00 ±0.025

Back Focal Length BFL (mm):

248.37
Effective Focal Length EFL (mm): 250.00
Coating: VS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 4.93
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 2.50
Radius R₁=R₂ (mm): 257.57
Clear Aperture CA (mm): 49.00
f/#: 5.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.10
Type: Double-Convex Lens
Wavelength Range (nm): 425 - 675
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View