

TECHSPEC[®] 5mm 532nm, Laser Line $\lambda/20$ High Tolerance Right Angle Mirror



Stock **#37-652** 8 In Stock

-

1

+

£191^{.20}

ADD TO CART

Volume Pricing	
Qty 1-5	£191.20 each
Qty 6-25	£156.80 each
Qty 26-49	£153.60 each
Need More?	Request Quote

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Right Angle Mirror

Type:

Physical & Mechanical Properties

5.00

Length of Legs (mm):

+0.00/-0.10

Dimensional Tolerance (mm):

	Bevel:
Protective as needed	
	Clear Aperture (%):
90	
	Length of Hypotenuse (mm):
7.10	

Optical Properties

	Surface Flatness (P-V):
$\lambda/20$	
Fused Silica (Corning 7980)	Substrate: ☐
	Surface Quality:
20-10	
	Coating Specification:
R _{abs} >99.8% @ 532nm @ 45° AOI R _{avg} >99.5% @ 523 - 537nm @ 45° AOI	
	Coating:
Laser Mirror (532nm)	
	Design Wavelength DWL (nm):
532	
	Pyramid Tolerance (arcmin):
±1	
	Angle Tolerance (arcsec):
±15	
	Damage Threshold, Reference: ☐
1MW/cm² @ 532nm	


Regulatory Compliance

	RoHS 2015:
Compliant	
	Reach 209:
Compliant	
	Certificate of Conformance:
View	

Product Details

- >99.5% Reflectivity at the Design Wavelength
- ±15 Arcsecond Angular Tolerance
- High Thermal Stability Substrates

TECHSPEC® Laser Line $\lambda/20$ High Tolerance Right Angle Mirrors are designed at Nd:YAG wavelengths with durable, high reflectivity dielectric coatings. Right angle mirrors are easily mounted and integrated into systems that redirect light 90°. With ±15 arcsecond angular tolerance and ±1 arcminute pyramid tolerance, these laser line mirrors simplify alignment when mounting. TECHSPEC® Laser Line $\lambda/20$ High Tolerance Right Angle Mirrors feature laser induced damage threshold specifications making them ideal for demanding laser applications.



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).