

5mm Dia., 0.5mm Thick, 2000-5000nm, High Durability AR Coated Sapphire Window



High Durability Anti-Reflection (AR) Coated Sapphire Windows

Stock **#18-467** **8 In Stock**

-

1

+

£120<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | £120.80 each                  |
| Qty 11-25      | £104.00 each                  |
| Qty 26-49      | £103.20 each                  |
| Need More?     | <a href="#">Request Quote</a> |

**i** Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Protective Window

Type:

Physical & Mechanical Properties

Protective as needed

Bevel:

Clear Aperture (%):

|             |                          |
|-------------|--------------------------|
| 90          |                          |
| 4.50        | Clear Aperture CA (mm):  |
| 5.00 ±0.05  | Diameter (mm):           |
| 0.50 ±0.05  | Thickness (mm):          |
| Fine Ground | Edges:                   |
| 1,900.00    | Knoop Hardness (kg/mm²): |
| ≤3.5        | Parallelism (arcmin):    |
| 0.27        | Poisson's Ratio:         |
| 435         | Young's Modulus (GPa):   |

| Optical Properties                                                               |                                                  |
|----------------------------------------------------------------------------------|--------------------------------------------------|
| 72.24                                                                            | Abbe Number (v <sub>d</sub> ):                   |
| Random                                                                           | Axis Orientation:                                |
| 0.008 for Visible Light Orthogonal to Optical Axis                               | Birefringence (n <sub>o</sub> -n <sub>e</sub> ): |
| Hardened BBAR (2000-5000nm)                                                      | Coating:                                         |
| R <sub>avg</sub> <1.5% @ 2000 - 5000nm<br>R <sub>abs</sub> <2.0% @ 2000 - 5000nm | Coating Specification:                           |
| 1.77                                                                             | Index of Refraction (n <sub>d</sub> ):           |
| Sapphire (Al <sub>2</sub> O <sub>3</sub> )                                       | Substrate:                                       |
| 2λ (typical)                                                                     | Surface Flatness (P-V):                          |
| 80-50                                                                            | Surface Quality:                                 |
| 2000 - 5000                                                                      | Wavelength Range (nm):                           |

|                                              |                           |
|----------------------------------------------|---------------------------|
| -80 to +160 per MIL-M-13508C Paragraph 4.4.4 | Coating Temperature (°F): |
|----------------------------------------------|---------------------------|

| Material Properties |                                                              |
|---------------------|--------------------------------------------------------------|
| 8.8                 | Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C): |
| 3.97                | Density (g/cm³):                                             |

| Environmental & Durability Factors                 |                          |
|----------------------------------------------------|--------------------------|
| Severe, per MIL-C-675C Paragraph 4.5.10            | Coating Abrasion:        |
| Per MIL-M-13508C Paragraph 4.4.6                   | Coating Adhesion:        |
| ≥24 Hours per MIL-C-675C paragraph 4.5.8           | Coating Humidity:        |
| ≥24 Hours Immersion per MIL-C-675C paragraph 4.5.7 | Coating Salt Solubility: |
| ≥24 Hours per MIL-C-675C paragraph 4.5.9           | Coating Salt Spray:      |

| Regulatory Compliance |                             |
|-----------------------|-----------------------------|
| <a href="#">View</a>  | Certificate of Conformance: |

## Product Details

- Achieves Severe Abrasion Requirements of MIL-C-675C
- Low Reflection Coatings for 400 - 1100nm or 2000 - 5000nm
- Ideal for Harsh Environments Requiring Thin Optics
- [Uncoated Sapphire Windows](#) are Also Available

High DurabilityAnti-Reflection (AR) Coated Sapphire Windows are designed for applications requiring the ruggedness of sapphire with AR coatings designed to survive severe abrasion. The AR coatings on these sapphire windows are designed to withstand temperature cycling from -80 to +160°F, salt sprayfor a continuous period of 24 hours, and salt solubilityfor an immersion period of 24 hours. Coating designs achieving the severe abrasion requirements of MIL-C-675C for VIS-NIR and MMIR applications are available, making them ideal for use in harsh environments. High DurabilityAnti-Reflection (AR) Coated Sapphire Windows are used in aerospace, defense, and industrial

applications, as well as any optical application requiring thin, durable protective windows.

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

---