


TECHSPEC®

50mm NIR II Coated, N-BK7 Right Angle Prism (Leg Coated)



Stock #26-779 **4 In Stock**

1 **£227^{.20}**

ADD TO CART

Volume Pricing	
Qty 1-5	£227.20 each
Qty 6-25	£181.60 each
Qty 26-49	£170.40 each
Need More?	Request Quote

Product Downloads	
STEP:step	Curve:pdf
PDF Drawing:pdf	IGES:igs
Curve (xlsx):xlsx	
eDrawing:eprt	
EO Spec Sheet	Download All

! Prices shown are exclusive of VAT/local taxes

General	
Type: Right Angle Prism	Note: Coating on Entrance/Exit Faces
Physical & Mechanical Properties	
Dimensional Tolerance (mm): +0.00/-0.10	Bevel: Protective as needed
Clear Aperture (%): 90	Length of Hypotenuse (mm): 70.70
Length of Legs (mm): 50.00	
Optical Properties	
Angle Tolerance (arcsec): ±15	Coating: NIR II (750-1550nm)
Substrate: N-BK7	Surface Quality: 40-20
Image Orientation: Left-Handed	Coating Specification: R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Ray Deviation (°): 90	Wavelength Range (nm): 750 - 1550
Damage Threshold, Reference: Entrance/Exit Faces: 8 J/cm ² @ 1064nm, 10ns	Power (fringes) @ 632.8nm: 1.25

Irregularity (fringes) @ 632.8nm: 0.25

Regulatory Compliance

RoHS 2015: **Compliant**

Certificate of Conformance: [View](#)

Reach 235: **Compliant**

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Ideal for Low Power Laser Sources
- Multiple BBAR Coatings Available
- Ray Deviation of 90°

TECHSPEC® Broadband Anti-Reflection (BBAR) Coated N-BK7 Right Angle Prisms (Leg Coated) are ideal for a range of low power laser line applications. These prisms feature tight angle tolerances and a precision N-BK7 substrate. The BBAR coating improves transmission efficiency when compared to uncoated right angle prisms. TECHSPEC® Broadband Anti-Reflection (BBAR) Coated N-BK7 Right Angle Prisms (Leg Coated) have their BBAR coating on entrance and exit faces. The prisms are available in lengths from 5 to 50mm.

Right angle prisms are generally used to bend image paths or redirect light at 90°. This produces a left-handed image and depending on the orientation of the prism, the image may be inverted or reverted. Right angle prisms can also be used in combination for image/beam displacement.

Technical Information


Right Angle Prism Ray Path

Right Angle Prism Ray Path

Right Angle Prism Tunnel Diagram

Right Angle Prism Tunnel Diagram

Frequently Purchased Together



#26-778 - 30mm NIR II Coated, N-BK7 Right Angle Prism (Leg Coated)
£139.20

Qty



Resources

Media Type

- Application Note
- Video
- FAQ
- Glossary

APPLICATION NOTE

Anti-Reflection
(AR) Coatings

APPLICATION NOTE

An
Introduction to
Optical
Coatings

VIDEO

Optical Prisms
Review

FAQ

I'd like to
adhere two
prisms
together. ho...

GLOSSARY

Dove Prism

GLOSSARY

Equilateral
(Dispersing)
Prism

[View More](#)