

# 50mm Travel, High Vacuum (10<sup>-6</sup> Torr) Motorized Linear Stage, Integrated Controller

See More by [Zaber™](#)



Stock **#74-699** NEW **1 In Stock**

-

1

+

£5,184<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | £5,184.00 each                |
| Need More?     | <a href="#">Request Quote</a> |

 Prices shown are exclusive of VAT/local taxes

Product Downloads

| General                                                          |                                 |
|------------------------------------------------------------------|---------------------------------|
| Metric                                                           | Type:                           |
| No                                                               | Encoder:                        |
| No/Yes                                                           | Manual Control/ LED Indicators: |
| Zaber Technologies Inc.                                          | Manufacturer:                   |
| X-LSM050A-SV2T9                                                  | Model Number:                   |
| Requires Accessory Kit, <a href="#">#75-301</a> , for operation. | Note:                           |
| 2-Phase Stepper                                                  | Type of Motor:                  |

| Physical & Mechanical Properties |                     |
|----------------------------------|---------------------|
| Linear (X)                       | Type of Movement:   |
|                                  |                     |
| Needle Roller Bearing            | Guide System:       |
|                                  |                     |
| 173.4 x 101.2                    | Stage Size (mm):    |
|                                  |                     |
| 50.8                             | Travel (mm):        |
|                                  |                     |
| 20                               | Accuracy (µm):      |
|                                  |                     |
| <12                              | Backlash (µm):      |
|                                  |                     |
| 21.4                             | Height (mm):        |
|                                  |                     |
| 10                               | Load Capacity (kg): |
|                                  |                     |
| 100                              | Load Capacity (N):  |
|                                  |                     |
| <3                               | Repeatability (µm): |
|                                  |                     |
| 0.000029 - 24                    | Speed (mm/s):       |
|                                  |                     |
| 35                               | Thrust (N):         |
|                                  |                     |
| 0.40                             | Weight (kg):        |
|                                  |                     |

| Optical Properties |                  |
|--------------------|------------------|
| 0.047              | Resolution (µm): |
|                    |                  |

| Electrical |                                 |
|------------|---------------------------------|
| 350        | Current (mA):                   |
|            |                                 |
| 350        | Maximum Operating Current (mA): |
|            |                                 |

| Hardware & Interface Connectivity                                                   |                     |
|-------------------------------------------------------------------------------------|---------------------|
| Lead Screw                                                                          | Type of Drive:      |
|                                                                                     |                     |
| 24-48 VDC; Power Supply w/US Plug found in accessories kit, <a href="#">#75-301</a> | Power Supply:       |
|                                                                                     |                     |
| RS-232, USB                                                                         | Computer Interface: |
|                                                                                     |                     |

| Material Properties                 |                       |
|-------------------------------------|-----------------------|
| High vacuum (10 <sup>-6</sup> Torr) | Vacuum Compatibility: |
|                                     |                       |

| Environmental & Durability Factors |                             |
|------------------------------------|-----------------------------|
| 0 to +50                           | Operating Temperature (°C): |
|                                    |                             |

| Regulatory Compliance     |                             |
|---------------------------|-----------------------------|
| <a href="#">Compliant</a> | RoHS 2015:                  |
|                           |                             |
| <a href="#">View</a>      | Certificate of Conformance: |
|                           |                             |
| <a href="#">Compliant</a> | Reach 247:                  |
|                           |                             |

## Product Details

- Low Vacuum (10<sup>-3</sup> Torr) and High Vacuum (10<sup>-6</sup> Torr) Options Available
- 360° Rotational, Linear, or Vertical Travel Stages, and Goniometer Options Available
- Controlled via Mnimal Feed-Through Wires

Zaber™ Vacuum Compatible Motorized Stages are designed for integration into vacuum systems and are available in high vacuum 10<sup>-6</sup> Torr stages or low vacuum 10<sup>-3</sup> Torr configurations (upon request). The stage body components are specifically engineered to limit outgassing of contaminants in the vacuum chamber, the included stepper motors are designed for thermal management in high vacuum environments, and the stages can be connected to a computer interface with minimal feed-through wires. Zaber™ Vacuum Compatible Motorized Stages are available in linear, 360° rotational, and goniometric configurations, allowing for a complete 6 Degree-of-Freedom system to be constructed in a vacuum. These stages are ideal for applications operating in high vacuum conditions, such as semiconductor manufacturing and processing, or optical coating processes.

**Note:** An accessories kit, [#75-301](#), is required and sold separately.

