

**TECHSPEC® 5mm FL f/4, Blue Series M12 Lens**



5mm FL Blue Series M12 Lens



Stock #69-260 **20+ In Stock**

⊖ 1 ⊕ £63<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-49       | £63.00 each                   |
| Qty 50+        | £50.00 each                   |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Blue Series **Product Family:**

M12 Imaging Lens **Type:**

**IR Cut Filter:**

No

**Imaging Lens Type:**

High Performance M12 Lens

## Physical & Mechanical Properties

**Iris Option:**

Fixed

**Length (mm):**

14.60

**Maximum Diameter (mm):**

14

**Outer Diameter (mm):**

14

**Weight (g):**

4

## Optical Properties

**Horizontal Field of View @ Max Sensor Format:**  
57.3°

**Field of View at Max Sensor Format:**  
Horizontal: 165.7mm - 57.3°  
Vertical: 117.5mm - 42.3°  
Diagonal: 225.4mm - 73.4°

**Horizontal Field of View, 1/3" Sensor:**  
165.6mm - 57.3°

**Horizontal Field of View, 1/4" Sensor:**  
117.5mm - 42.3°

**Maximum Image Circle (mm):**

6.00

**Numerical Aperture NA, Object Side:**

0.0040

**Number of Elements (Groups):**

6(5)

**Wavelength Range (nm):**

400 - 700

**Focal Length FL (mm):**

5.00

**Working Distance (mm):**

150 - ∞

**Aperture (f/#):**

f/4

**Distortion (%):**

-18.88 @ Full Field

**Back Focal Length BFL (mm):**

4.0 - 3.9

**Coating Specification:**

M4 MgF<sub>2</sub> @ 550nm

**Entrance Pupil Position (mm):**

2.74

**Object Space Principal Plane (mm):**

5.94

**Image Space Principal Plane (mm):**

2.53

**Maximum Distortion (%):**

-18.88

**Exit Pupil Position (mm):**

-6.51

**Lens Wavelength Range:**

VIS

## Sensor

**Maximum Sensor Format:**

1/3"

**Pixel Size (µm):**

1.40

## Threading & Mounting

**Filter Thread:**

N/A

**Mount:**

S-Mount (M12 x 0.5)

## Regulatory Compliance

**RoHS 2015:**

Compliant

## Product Details

- Up to 1/2", S-Mount Lens
- Up to 5 MegaPixels, 1.4µm Pixel Size Sensors
- High Resolution Board Camera Lens Optimized for Close WD
- 2mm to 35mm Focal Length
- **Ruggedized Designs** Also Available


TECHSPEC® Blue Series M12 Lenses feature high resolution performance, along with the same great versatility of our **TECHSPEC® Green Series M12 Lenses**. Each lens consists of several precision glass elements mounted in a compact, aluminum housing. These lenses can connect to C-Mount cameras using the M12 x 0.5 Adapter for C-Mount Cameras (**#53-675**) or the M12 x 0.5 C-Mount Adapter with Rubber O-Ring (**#59-241**) for vibration-sensitive environments. TECHSPEC® Blue Series M12 Lenses are ideal for automotive, industrial, and medical imaging application. Prescription data is available by submitting a [Request for Prescription Form](#).

**Note:** Compatible **TECHSPEC® M12 Imaging Lens Accessories** available.


Edmund Optics has created multiple product families of our TECHSPEC® M12 S-Mount Lenses, which are designed to provide high resolution. These high performance lenses feature precision glass designs in a metal housing and have optimized specifications between each product family to meet your application needs.

- **Blue Series M12 Lenses:** High resolution finite conjugate designs optimized for machine vision working distances.
- **Rugged Blue Series M12 Lenses:** Stabilized ruggedization versions of our Blue Series M12 Lenses, utilizing the same optics.
- **Green Series M12 Lenses:** Finite conjugate designs optimized for machine vision working distances.
- **Red Series M12 Lenses:** Infinite conjugate designs optimized for high resolution performance out to infinity.
- **HEO Series M12 Lenses:** Harsh Environment Optics (HEO) sealed versions of our Red Series M12 Lenses.
- **Liquid Lens M12 Lenses:** Integrated liquid lens for fast electronic focus.


## Technical Information




#69-260, 5mm FL f/4, Blue Series M12 Lens, Distortion Plot




#69-260, 5mm FL f/4, Blue Series M12 Lens, Relative Illumination Plot




#69-260, 5mm FL f/4, Blue Series M12 Lens, Working Distance versus Field of View Plot




#69-260, 5mm FL f/4, Blue Series M12 Lens, Modulated Transfer Function (MTF) Plot, 150mm Working Distance, f4



#69-260, 5mm FL f/4, Blue Series M12 Lens, Depth of Field Plot, 150mm Working Distance, f4



#69-260, 5mm FL f/4, Blue Series M12 Lens, Modulated Transfer Function (MTF) Plot, 250mm Working Distance, f4



#69-260, 5mm FL f/4, Blue Series M12 Lens, Depth of Field Plot, 250mm Working Distance, f4

| Focal Length | A      | B      | C*          | D      |
|--------------|--------|--------|-------------|--------|
| 2.0mm        | 18.0mm | 21.7mm | 2.26mm      | 4.75mm |
| 3.0mm        | 14.0mm | 17.1mm | 4.8 - 4.7mm | 5.8mm  |
| 4.0mm        | 14.0mm | 19.7mm | 6.1 - 6.0mm | 4.4mm  |
| 5.0mm        | 14.0mm | 14.6mm | 4.0 - 3.9mm | 3.7mm  |
| 6.0mm        | 14.0mm | 14.1mm | 6.9 - 6.8mm | 4.5mm  |
| 8.0mm        | 14.0mm | 12.3mm | 8.8 - 8.6mm | 3.7mm  |
| 10.0mm       | 14.0mm | 17.0mm | 6.6 - 6.3mm | 3.7mm  |

|        |        |        |                |        |
|--------|--------|--------|----------------|--------|
| 12.5mm | 15.0mm | 22.9mm | 10.1 - 9.7mm   | 4.8mm  |
| 17.5mm | 14.0mm | 20.7mm | 5.8 - 4.9mm    | 7.6mm  |
| 25.0mm | 18.0mm | 30.0mm | 8.5 - 6.5mm    | 11.5mm |
| 35.0mm | 18.0mm | 29.5mm | 18.72 - 14.0mm | 14.5mm |



\*Specified for Optimized Working Distance of 150 - 250mm.

;