

TECHSPEC® 532nm CWL, 25mm Dia, 2nm Bandwidth, OD 6 Laser Line Bandpass Filter



Stock **#68-970** ☐ In Stock

[Additional Bandwidths](#)



1



£565.25

ADD TO CART

Qty 1-9

£565.25

Qty 10+

£497.25

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00

Angle of Incidence (°):
0 ±2

Bandwidth (nm):

2.00
OD 5 Blocking Wavelength Range (nm) : 447 - 527 & 537 - 699
OD 6 Blocking Wavelength Range (nm): 489 - 524 & 540 - 585
Optical Density OD (Average): ≥6.0
Clear Aperture CA (mm): 21.00
Center Wavelength CWL (nm): 532.00
Design Wavelength DWL (nm): 532
Full Width-Half Max FWHM (nm): 3.70
Substrate: ☐ Fused Silica (Corning 7980)
Coating: Hard Coated
Surface Quality: 60-40
Thickness Tolerance (mm): +0.0/-0.1
Transmission (%): ≥90
Type: Bandpass Filter
Durability: Environmental: MIL-STD-810F, sect. 507.4 Durability: MIL-C-48497A, sect. 3.4.1
Transmitted Wavefront, RMS: <i>M4 @ 633nm</i>
Mount Thickness (mm): 3.5

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View