

561nm High Performance Laser Line Filter 25mm Dia.



High Performance Laser Line Bandpass Filters

Stock **#12-279** **2 In Stock**

☐ [Additional Bandwidths](#)

-

1

+

£764⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£764.00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Bandpass Filter	Type:
Physical & Mechanical Properties	
25.00 +0.0/-0.1	Diameter (mm):
≥22	Clear Aperture CA (mm):

±0.10	Thickness Tolerance (mm):
Mounted in Black Anodized Ring	Construction:
Physical Durability: ML-C-48497A Paragraphs 4.5.3.1, 4.5.3.2, 4.5.3.3, 4.5.4.2, and 4.5.5.3	
2.0 ±0.1	Substrate Thickness (mm):
Optical Properties	
0 ±2	Angle of Incidence (°):
2.1	Bandwidth (nm):
OD 5 Blocking Wavelength Range (nm) : 466.7 - 555.4 & 566.6 - 750.5	
OD 6 Blocking Wavelength Range (nm): 516.1 - 552.6 & 569.4 - 617.1	
≥6.0	Optical Density OD (Average):
561.00	Center Wavelength CWL (nm):
561	Design Wavelength DWL (nm):
2.10 - 3.9	Full Width-Half Max FWHM (nm):
Fused Silica	Substrate: ☐
>90	Minimum Transmission (%):
Hard Coated	Coating:
60-40	Surface Quality:
>90	Transmission (%):
Blocking Wavelength Range (nm): 466.7 - 555.4 & 566.6 - 750.5	
Threading & Mounting	
3.5 ±0.1	Mount Thickness (mm):
Environmental & Durability Factors	
Environmental Durability: ML-STD-810F Paragraphs 501.4, 502.4, and 507.4	
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 209:
View	Certificate of Conformance:







Product Details

- Over 90% Transmission at Specified Laser Lines
- Hard Coated Design
- Designed for Laser Applications

Available for use with common gas and solid state lasers, High Performance Laser-Line Bandpass Filters are designed to offer maximum transmission of stimulated emission, while eliminating noisy spontaneous emission. These laser line filters are available at popular diode and Nd:YAG laser lines, including 532nm, 785nm, and 1064nm. High Performance Laser-Line Bandpass Filters are ideal for laser-based fluorescence instrumentation, Raman spectroscopy, or for analytical or medical laser systems. Due to their steep edges, High Performance Laser-Line Bandpass Filters are excellent complements to TECHSPEC® Notch Filters and [Laser Line Longpass Filters](#).

Note: These filters are optimized for high spectral performance rather than high Laser Induced Damage Thresholds (LIDT). A typical LIDT for these filters is 0.1 J/cm² @ 532nm, 10ns.

Technical Information



Compatible Mounts