

600 Grooves/mm, 50mm Sq, UV Transmission Grating Beamsplitter



Stock **#85-297** 1 In Stock

-

1

+

£295^{.04}

ADD TO CART

Volume Pricing	
Qty 1-9	£295.04 each
Qty 10-24	£265.28 each
Qty 25-49	£239.01 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Transmission Diffraction Grating

Type:

Physical & Mechanical Properties	
50.00 x 50.00	Dimensions (mm):
90	Clear Aperture (%):
Blazed Grating	Construction:
50.00	Length (mm):
2.00 ±0.5	Thickness (mm):
50.00	Width (mm):
±0.5	Alignment of Grooves to Edge (°):
Optical Properties	
600	Groove Density (grooves/mm):
250 - 600	Wavelength Range (nm):
22.0	Blaze Angle (°):
Fused Silica (Corning 7980)	Substrate: ☐
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:


PRODUCT DETAILS

- Multiple Diffraction Angles Available
- UV Grade Fused Silica Substrate
- Ideal for Fixed Grating Applications

Ideal for spectrographs and other compact systems using small detector arrays, UV Transmission Gratings are a simplistic means of dispersing light for fixed grating applications in the 250 – 450nm wavelength range. As incident light strikes the UV Transmission Gratings' coarse groove spacing, it is dispersed on the opposite side of the grating at a fixed angle. As groove spacing increases, the diffraction angle decreases. UV Transmission Gratings are relatively polarization insensitive and are fairly insensitive to alignment errors.

Handling Gratings: Gratings require special handling, making them prone to fingerprints and aerosols. Gratings should only be handled by the edges. Before attempting to clean a grating, please [contact us](#).

TECHNICAL INFORMATION



SPECIAL HANDLING

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools
