

TECHSPEC® 600 x 1000mm Linear Polarizing Film (XP42-18) with Adhesive



Stock **#29-491** **10 In Stock**

⊖ 1 ⊕ £352.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	£352.00 each
Qty 11-25	£309.28 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Linear Polarizer

Type:

Note:
Polarization axis is parallel to first listed dimension

Physical & Mechanical Properties

600.0 x 1000.0 +5.0/0.0

Dimensions (mm):

Thickness (mm):
0.22 ±0.03

Construction:
Polarizing Film

Optical Properties

Coating:
Pressure Sensitive Adhesive (PSA) one-sided

Extinction Ratio:
9000:1 (nominal at 555nm)

Substrate:
[Polymer Film XP42-18](#)

Transmission (%):
Single: 42 ±2
Parallel: 36.4
Crossed: <0.004 (nominal at 555nm)

Wavelength Range (nm):
400 - 700

Polarization Efficiency (%):
>99.98 (nominal at 555nm)

Transmission, Single (%):
42 ±2

Transmission, Parallel (%):
36.4

Transmission, Crossed (%):
<0.004 (nominal at 555nm)

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 247:
[Compliant](#)

Product Details

- High Transmission of Unpolarized Light from 400 – 700nm
- Excellent Extinction Ratio of 9000:1
- Available in Custom Sizes
- [High-Temperature](#) Options Also Available



Ideal for a range of imaging applications, TECHSPEC® High Contrast Linear Polarizing Film (XP42) features an excellent extinction ratio and high transmission from 400 – 700nm. This polarizing film is offered in multiple thicknesses; thicker polarizing film has increased rigidity. Available in sheets, TECHSPEC® High Contrast Linear Polarizing Film (XP42) can be cut to fit any application need.

Note: Polarizer Film with adhesive available.

Immediate Custom Quotes Available

If you have a need for any round, square, or rectangular size of a TECHSPEC High Contrast Linear Polarizing Film (XP42) in dimensions between 3mm and 600mm, please visit our [Polarizing Film Tool](#). We'll provide an immediate quote, and can deliver the part to your requested size in approximately 3 weeks. A full list of standard manufacturing tolerances and restrictions are listed. For fully customized polymer polarizers to your requirements, visit our [Customized Polymer Polarizers Capabilities](#) page.

Technical Information



XP44 - Linear Polarizer

